



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10524 W US Hwy 80
75126-0000, TX Forney
Phone: 972-210-2783
Fax: 972-210-2784



PS20AC1 20A 120/277VAC B+S Wire SP SW BN

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | PS20AC1 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V |
| Weight per unit | 0.2142 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|---------------------|--|
| action | Single pole |
| actuator | Toggle |
| amperage rating | 20 |
| Contact Rating | 20 Amp, 120/277 VAC |
| indoor/outdoor | Indoor |
| insulation | False |
| Load Rating | 20 A @ 120/277 VAC |
| Load Type | Halogen, Fluorescent, CFL, Xenon, LED, Incandescent, Universal |
| Material | Thermoplastic |
| Mounting Type | Wall Box |
| Number of Gangs | 1 |
| Number of Switches | 1.0 |
| Poles | 1 |
| Switch Type | Toggle |
| throw type | Single Throw |
| Voltage | 120/277 V |
| Voltage Rating | 120/277 |
| Wall Plate Included | NO |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|--|
| Description | 20A 120/277VAC B+S WIRE SP SW BN |
| extra long description | P&S PS20AC1 20A 120/277VAC B+S WIRE |
| Features | Chemical Resistant |
| Long Description | 1-Pole Toggle Switch, Back and Side-Wire, 20A 120/277V |
| Product Type | 20A 120/277VAC B+S Wire SP SW BN |
| Special Features | Back & side wire, locking support, heavy duty toggle |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10524 W US Hwy 80
75126-0000, TX Forney
Phone: 972-210-2783
Fax: 972-210-2784

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007195200 |
| Manufacturers Part Number | PS20AC1 |
| UPC | 785007195200 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Industrial switches |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.2142 |

Uses, Certifications, and Standards

| | |
|----------------------|--|
| Application | Industrial Spec Grade |
| Enclosure | Nylon |
| Mounting standard | WALL FEDSPEC, CULUS, UL 498/20, FEDSPEC |