

Eaton PSG120E

Catalog Number: PSG120E

Power Supply, 120W, Single-phase, 100-240V input voltage, 24 Vdc \pm 2% output voltage, 1.4A input current, 5A output current, less than 80A inrush current, 47-63 Hz, 85-264V, 120-375 Vdc, Aluminum enclosure, Heavy-duty screw terminals



Photo is representative

General specifications

Product Name	Catalog Number
Eaton PSG general purpose power supply	PSG120E
	UPC
	786685215440

Product Length/Depth	Product Height
4.76 in	4.53 in

Product Width	Product Weight
1.97 in	0.81 lb

Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year German Safety from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	CE Marked RoHS Compliant

Certifications

- UL 508
- cULus/UL 60950-1
- CSA Certified
- IEC Rated
- cUL Certified
- EN Listed

Catalog Notes

Ratings for single-phase are at 115V. 0 Hz at DC input.

defaultTaxonomyAttributeLabel

Special features

Varistor transient surge voltage, surge voltage protection against internal surge, safety class 1 with ground connection, finger-safe cover

Operating temperature - max

75 °C

Operating temperature - min

-20 °C

Power consumption

120 W

Phase

Single-phase

Voltage rating

85-264 Vac, 100-375 Vdc

Frequency rating

47-63 Hz

Enclosure material

Aluminum

Output voltage

24 V

Terminals

Heavy-duty screw

Input voltage

100-240 Vac

Series

PSG

Rated operational current

7.5 A surge

Less than 80 A inrush

5 A output

1.4 A input

Resources

Brochures

[Eaton's PSG Series Power Supplies](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[PSG120E AutoCAD 2D Footprint \(mm\)](#)

Installation instructions

[Installation Instructions for PSG120E Power Supply](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - PSG120E](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)