



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3700 Pasadena Fwy
77503-0000, TX Pasadena
Phone: 281-220-3780
Fax: 713-740-6104



PV4090EL00 4IN PVC Coated Rigid 90

Calpipe Industries, Inc

Catalog Number	PV4090EL00
Manufacturer	Calpipe Industries, Inc
Description	PVC Coated Steel Rigid Conduit Standard Radius Elbow, Standard Radius Type; Steel Material; 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior Finish; UL 6, UL Approval; ANSI C80.1, NEMA RN-1 Applicable Standard; 1 Standard Package
Weight per unit	36.8 (lbs/each)
Product Category	Steel

Features

Applicable Standard	ANSI C80.1, NEMA RN-1
Bend Angle	90 Degree
Bend Radius	16 INCH
End Type	THREADED
Material	Steel

Material, Color, and Finish

Finish	0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior
--------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3700 Pasadena Fwy
77503-0000, TX Pasadena
Phone: 281-220-3780
Fax: 713-740-6104

Descriptions

Additional Information

Length 21 Inch; Constructional Feature Corrosion Resistant; Application Petrochemical, Water and Wastewater Treatment Facility, Transportation and Infrastructure, Food, Dairy and Beverage, Mining, Marine and Coastal Facility, Chemical Plants, Steel Mills,

Commodity Description

ELBOWS-COUPINGS-NIPPLES - STEEL

Description

4IN PVC COATED RIGID 90

extra long description

STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 1 STANDARD PACKAGE; 4 INCH TRADE SIZE; THREADED END TYPE; 90 DEGREE BEND ANGLE; 16 INCH BEND RADIUS; LENGTH 21 INCH; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; APPLICATION PETROCHEMICAL, WATER AND WASTEWATER TREATMENT FACILITY, TRANSPORTATION AND INFRASTRUCTURE, FOOD, DAIRY AND BEVERAGE, MINING, MARINE AND COASTAL FACILITY, CHEMICAL

Long Description

PVC COATED STEEL RIGID CONDUIT STANDARD RADIUS ELBOW, STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 1 STANDARD PACKAGE

Product Type

PVC Coated Steel Rigid Conduit Standard Radius Elbow

Manufacturer Information

Brand

Calpipe Industries, Inc

GTIN

00847656053963

Manufacturers Part Number

PV4090EL00

Model

PV

UPC

847656053963

Taxonomies, Classifications, and Categories

Category Description

DIECAST EMT FITTINGS

Type

STANDARD RADIUS

Trade Size

Trade Size

4 INCH

Packaging

Carton

1

Standard Package

1

Weight Per each

36.75

Uses, Certifications, and Standards

Approval

UL 6, CUL