



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT5362LA Duplex Recp Spec GRD 20A/125V La

Pass & Seymour/LeGrand

| | |
|------------------|--|
| Catalog Number | PT5362LA |
| Manufacturer | Pass & Seymour/LeGrand |
| Description | Plugtail Spec Grade Duplex Receptacle 20AMP 125VOLT Light Almond |
| Weight per unit | 0.2300 (lbs/each) |
| Product Category | Gen Purpose Recept & Surge Pro |

Features

| | |
|---------------------|--|
| amperage rating | 20 |
| Dielectric Strength | Withstands 2000V minimum |
| indoor/outdoor | Indoor |
| Material | Nylon |
| media | Yes |
| Number of Wires | 3 |
| Outlet Type | Indoor, Commercial |
| Poles | Double Pole |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wattage | Electrical power is expressed in Amps and Volts. |
| Wire Size | 12 |

Dimensions and Weight

| | |
|--------|-------|
| Height | 3.281 |
| Width | .625 |

Descriptions

| | |
|------------------------|---|
| Description | DUPLEX RECP SPEC GRD 20A/125V LA |
| extra long description | P&S PT5362LA DUP RECEPT SPEC GRD 20 |
| Long Description | PlugTail Spec Grade Duplex Receptacle 20amp 125volt Light Almond |
| Product Type | Dup Recept Spec GRD 20A/125V La |
| Special Features | Plated steel wrap strap design for maximum durability and corrosion resistance. .036 inch thick, brass, triple-wipe power contacts for lasting retention. Three drive screws anchor strap to back body and face. No exposed terminals create a finger safe application before, during, and after installation. Built-in connector features large brass terminal blades to ensure consistent, reliable electrical connections. Crimped and welded contacts. Ultrasonically welded polycarbonate connector housing secures termin |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007091700 |
| Manufacturers Part Number | PT5362-LA |
| UPC | 785007091700 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------|
| Category Description | Residential Switches |
| Type | Outlet |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 100 |
| Weight Per each | 0.23 |

Uses, Certifications, and Standards

| | |
|--------------------------|-----------------------------|
| Application | Commercial |
| environmental conditions | Flammability: UL94 V2 |
| Mounting | WALL |
| nema rating | 5-20R |
| standard | FEDSPEC, CULUS, cULus UL498 |
| Temperature Rating | -40° - 60° C |