

PVC Entrance Caps with Adapters/Sleeves

NEW!
more on
reverse

Save Money • Reduce Inventory



PVC109
Fits 4" -
Includes adapters for 3"
and 3.5"

Made of UV rated plastic for long outdoor life, Arlington's entrance caps come with adapters that fit a range of sizes, so you'll have *fewer products to stock*.

Our new PVC1020 handles 1/2", 3/4" and 1" PVC, rigid and EMT – one product for all three sizes. Used for 1/2", PVC1020 costs less than a comparably sized aluminum cap. The savings is even greater on the 3/4" and 1" sizes!

NEW!



PVC1020
*sleeves and bushings
shown combined

PVC1040 fits 1-1/4" and 1-1/2" PVC, rigid and EMT.



PVC1040
Includes sleeves/bushing
for 1-1/4 and 1-1/2

Save money – and the hassle of stocking extra inventory with *FIVE* 1/2" to 4" clamp-on caps that fit *TEN* trade sizes of rigid, EMT and PVC!



Arlington
1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

PVC Entrance Caps

with Adapters and Bushings to fit a Range of Sizes



PVC1020 Installation Guidelines

1" RIGID	No bushing or sleeve needed
1" EMT	Use 1" EMT sleeve
3/4" RIGID	Use 3/4" reducing bushing
3/4" EMT	Use 3/4" bushing and 3/4" EMT sleeve
1/2" RIGID	Use 1/2" reducing bushing
1/2" EMT	Use 1/2" bushing and 1/2" EMT sleeve

Tighten screws fully to secure weatherhead assembly to the conduit.



PVC1040 Installation Guidelines

1-1/2" RIGID	No bushing or sleeve needed
1-1/2" EMT	Use 1-1/2" EMT sleeve
1-1/4" RIGID	Use 1-1/4" reducing bushing
1-1/4" EMT	Use 1-1/4" bushing and 1-1/4" EMT sleeve

Tighten screws fully to secure weatherhead assembly to the conduit.

UV rated for long outdoor life.



Arlington
 1 Stauffer Industrial Park
 Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.arlingtonlowvoltage.com
www.aifittings.com

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	TRADE SIZE (INCHES)	ENTRANCE CAPS UV Rated Plastic for Long Outdoor Life	STD PKG
PVC1020	73146	1/2, 3/4, 1	Combo style, w/ adapter sleeves and bushings for EMT and Rigid	20
PVC1040	73147	1-1/4, 1-1/2	Combo style, w/ adapter sleeves and bushing for EMT and Rigid	10
PVC105	73105	2	For rigid, w/ adapter sleeve for EMT	5
PVC106	12512	2-1/2		1
PVC109	12513	3, 3-1/2, 4	Combo style, w/ adapter sleeves for 3" and 3-1/2"	1

Distributed by

PVC Entrance Caps with Adapters/Sleeves

NEW!
more on
reverse

Save Money • Reduce Inventory



PVC109
Fits 4" -
Includes adapters for 3"
and 3.5"

Made of UV rated plastic for long outdoor life, Arlington's entrance caps come with adapters that fit a range of sizes, so you'll have *fewer products to stock*.

Our new PVC1020 handles 1/2", 3/4" and 1" PVC, rigid and EMT – one product for all three sizes. Used for 1/2", PVC1020 costs less than a comparably sized aluminum cap. The savings is even greater on the 3/4" and 1" sizes!

NEW!



PVC1020
*sleeves and bushings
shown combined

PVC1040 fits 1-1/4" and 1-1/2" PVC, rigid and EMT.



PVC1040
Includes sleeves/bushing
for 1-1/4 and 1-1/2

Save money – and the hassle of stocking extra inventory with *FIVE* 1/2" to 4" clamp-on caps that fit *TEN* trade sizes of rigid, EMT and PVC!



Arlington
1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

PVC Entrance Caps

with Adapters and Bushings to fit a Range of Sizes



PVC1020 Installation Guidelines

1" RIGID	No bushing or sleeve needed
1" EMT	Use 1" EMT sleeve
3/4" RIGID	Use 3/4" reducing bushing
3/4" EMT	Use 3/4" bushing and 3/4" EMT sleeve
1/2" RIGID	Use 1/2" reducing bushing
1/2" EMT	Use 1/2" bushing and 1/2" EMT sleeve

Tighten screws fully to secure weatherhead assembly to the conduit.



PVC1040 Installation Guidelines

1-1/2" RIGID	No bushing or sleeve needed
1-1/2" EMT	Use 1-1/2" EMT sleeve
1-1/4" RIGID	Use 1-1/4" reducing bushing
1-1/4" EMT	Use 1-1/4" bushing and 1-1/4" EMT sleeve

Tighten screws fully to secure weatherhead assembly to the conduit.

UV rated for long outdoor life.



Arlington
 1 Stauffer Industrial Park
 Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.arlingtonlowvoltage.com
www.aifittings.com

CATALOG NUMBER	UPC/DCI/NAED MFG #01 8997	TRADE SIZE (INCHES)	ENTRANCE CAPS UV Rated Plastic for Long Outdoor Life	STD PKG
PVC1020	73146	1/2, 3/4, 1	Combo style, w/ adapter sleeves and bushings for EMT and Rigid	20
PVC1040	73147	1-1/4, 1-1/2	Combo style, w/ adapter sleeves and bushing for EMT and Rigid	10
PVC105	73105	2	For rigid, w/ adapter sleeve for EMT	5
PVC106	12512	2-1/2		1
PVC109	12513	3, 3-1/2, 4	Combo style, w/ adapter sleeves for 3" and 3-1/2"	1

Distributed by