

PVC Entrance Caps with Adapters/Sleeves

NEW!
more on
reverse

Save Money • Reduce Inventory



PVC109
Fits 4" -
Includes adapters for 3"
and 3.5"

Made of UV rated plastic for long outdoor life, Arlington's entrance caps come with adapters that fit a range of sizes, so you'll have *fewer products to stock*.

Our new PVC1020 handles 1/2", 3/4" and 1" PVC, rigid and EMT – one product for all three sizes. Used for 1/2", PVC1020 costs less than a comparably sized aluminum cap. The savings is even greater on the 3/4" and 1" sizes!

NEW!



PVC1020
*sleeves and bushings
shown combined

PVC1040 fits 1-1/4" and 1-1/2" PVC, rigid and EMT.



PVC1040
Includes sleeves/bushing
for 1-1/4 and 1-1/2

Save money – and the hassle of stocking extra inventory with *FIVE* 1/2" to 4" clamp-on caps that fit *TEN* trade sizes of rigid, EMT and PVC!



Arlington
1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

PVC Entrance Caps

with Adapters and Bushings to fit a Range of Sizes



PVC1020 Installation Guidelines

| | |
|-------------------|--------------------------------------|
| 1" RIGID | No bushing or sleeve needed |
| 1" EMT | Use 1" EMT sleeve |
| 3/4" RIGID | Use 3/4" reducing bushing |
| 3/4" EMT | Use 3/4" bushing and 3/4" EMT sleeve |
| 1/2" RIGID | Use 1/2" reducing bushing |
| 1/2" EMT | Use 1/2" bushing and 1/2" EMT sleeve |

Tighten screws fully to secure weatherhead assembly to the conduit.



PVC1040 Installation Guidelines

| | |
|---------------------|--|
| 1-1/2" RIGID | No bushing or sleeve needed |
| 1-1/2" EMT | Use 1-1/2" EMT sleeve |
| 1-1/4" RIGID | Use 1-1/4" reducing bushing |
| 1-1/4" EMT | Use 1-1/4" bushing and 1-1/4" EMT sleeve |

Tighten screws fully to secure weatherhead assembly to the conduit.

UV rated for long outdoor life.



Arlington
 1 Stauffer Industrial Park
 Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.arlingtonlowvoltage.com
www.aifittings.com

| CATALOG NUMBER | UPC/DCI/NAED MFG #01 8997 | TRADE SIZE (INCHES) | ENTRANCE CAPS UV Rated Plastic for Long Outdoor Life | STD PKG |
|----------------|---------------------------|---------------------|--|---------|
| PVC1020 | 73146 | 1/2, 3/4, 1 | Combo style, w/ adapter sleeves and bushings for EMT and Rigid | 20 |
| PVC1040 | 73147 | 1-1/4, 1-1/2 | Combo style, w/ adapter sleeves and bushing for EMT and Rigid | 10 |
| PVC105 | 73105 | 2 | For rigid, w/ adapter sleeve for EMT | 5 |
| PVC106 | 12512 | 2-1/2 | | 1 |
| PVC109 | 12513 | 3, 3-1/2, 4 | Combo style, w/ adapter sleeves for 3" and 3-1/2" | 1 |

Distributed by

PVC Entrance Caps with Adapters/Sleeves

NEW!
more on
reverse

Save Money • Reduce Inventory



PVC109
Fits 4" -
Includes adapters for 3"
and 3.5"

Made of UV rated plastic for long outdoor life, Arlington's entrance caps come with adapters that fit a range of sizes, so you'll have *fewer products to stock*.

Our new PVC1020 handles 1/2", 3/4" and 1" PVC, rigid and EMT – one product for all three sizes. Used for 1/2", PVC1020 costs less than a comparably sized aluminum cap. The savings is even greater on the 3/4" and 1" sizes!

NEW!



PVC1020
*sleeves and bushings
shown combined

PVC1040 fits 1-1/4" and 1-1/2" PVC, rigid and EMT.



PVC1040
Includes sleeves/bushing
for 1-1/4 and 1-1/2

Save money – and the hassle of stocking extra inventory with *FIVE* 1/2" to 4" clamp-on caps that fit *TEN* trade sizes of rigid, EMT and PVC!



Arlington
1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.aifittings.com

PVC Entrance Caps

with Adapters and Bushings to fit a Range of Sizes



PVC1020 Installation Guidelines

- 1" RIGID** No bushing or sleeve needed
- 1" EMT** Use 1" EMT sleeve
- 3/4" RIGID** Use 3/4" reducing bushing
- 3/4" EMT** Use 3/4" bushing and 3/4" EMT sleeve
- 1/2" RIGID** Use 1/2" reducing bushing
- 1/2" EMT** Use 1/2" bushing and 1/2" EMT sleeve

Tighten screws fully to secure weatherhead assembly to the conduit.



PVC1040 Installation Guidelines

- 1-1/2" RIGID** No bushing or sleeve needed
- 1-1/2" EMT** Use 1-1/2" EMT sleeve
- 1-1/4" RIGID** Use 1-1/4" reducing bushing
- 1-1/4" EMT** Use 1-1/4" bushing and 1-1/4" EMT sleeve

Tighten screws fully to secure weatherhead assembly to the conduit.

UV rated for long outdoor life.



1 Stauffer Industrial Park
Scranton, PA 18517
800/233.4717
Fax 570/562.0646
www.arlingtonlowvoltage.com
www.aifittings.com

| CATALOG NUMBER | UPC/DCI/NAED MFG #01 8997 | TRADE SIZE (INCHES) | ENTRANCE CAPS UV Rated Plastic for Long Outdoor Life | STD PKG |
|----------------|---------------------------|---------------------|--|---------|
| PVC1020 | 73146 | 1/2, 3/4, 1 | Combo style, w/ adapter sleeves and bushings for EMT and Rigid | 20 |
| PVC1040 | 73147 | 1-1/4, 1-1/2 | Combo style, w/ adapter sleeves and bushing for EMT and Rigid | 10 |
| PVC105 | 73105 | 2 | For rigid, w/ adapter sleeve for EMT | 5 |
| PVC106 | 12512 | 2-1/2 | | 1 |
| PVC109 | 12513 | 3, 3-1/2, 4 | Combo style, w/ adapter sleeves for 3" and 3-1/2" | 1 |

Distributed by