



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV2000ST6 2IN PVC Coated Myers Hub

Calpipe Industries, Inc

Catalog Number	PV2000ST6
Manufacturer	Calpipe Industries, Inc
Description	Conduit Hub, Threaded Type; 0.002 Inch Urethane Coated Interior/0.04 Inch PVC Coated Exterior Steel Material; 4.25 Inch Diameter X 3.75 Inch Length Size; Conduit Used On; UI 6/514B, Nec/Cec Approval; Non-Grounding; 2 Inch Trade Size; Corrosion Resistant
Weight per unit	N/A
Product Category	PVC Conduit Fittings & Accy

Features

Ground Type	Non-Grounding
Material	0.002 Inch Urethane Coated Interior/0.04 Inch PVC Coated Exterior Steel

Dimensions and Weight

Size	4.25 Inch Diameter x 3.75 Inch Length
------	---------------------------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	Maximum Wall Thickness 0.125 Inch; Enclosure Type Class I Div 2, Class II Div 1 and 2, Class III Div 1 and 2, Class I Zone 1 AEx e II, Class I Zone 1 Ex e II, NEMA 2/3/3R/4/4X/11/12; Application Petrochemical, Water and Wastewater Treatment Facility, Tran
Commodity Description	PVC CONDUIT FITTINGS & ACCESSORIES
Description	2IN PVC COATED MYERS HUB
extra long description	THREADED TYPE; 0.002 INCH URETHANE COATED INTERIOR/0.04 INCH PVC COATED EXTERIOR STEEL MATERIAL; 4.25 INCH DIAMETER X 3.75 INCH LENGTH SIZE; CONDUIT USED ON; UL 6/514B, NEC/CEC APPROVAL; NON-GROUNDING; 2 INCH TRADE SIZE; CORROSION RESISTANT; MAXIMUM WALL THICKNESS 0.125 INCH; ENCLOSURE TYPE CLASS I DIV 2, CLASS II DIV 1 AND 2, CLASS III DIV 1 AND 2, CLASS I ZONE 1 AEX E II, CLASS I ZONE 1 EX E II, NEMA 2/3/3R/4/4X/11/12; APPLICATION PETROCHEMICAL, WATER AND WASTEWATER TREATMENT FACILITY, TRANSPORTATION AND
Long Description	CONDUIT HUB, THREADED TYPE; 0.002 INCH URETHANE COATED INTERIOR/0.04 INCH PVC COATED EXTERIOR STEEL MATERIAL; 4.25 INCH DIAMETER X 3.75 INCH LENGTH SIZE; CONDUIT USED ON; UL 6/514B, NEC/CEC APPROVAL; NON-GROUNDING; 2 INCH TRADE SIZE; CORROSION RESISTANT
Product Type	Conduit Hub

Manufacturer Information

Brand	Calpipe Industries, Inc
GTIN	00847656076214
Manufacturers Part Number	PV2000ST6
Model	ST
UPC	847656076214

Taxonomies, Classifications, and Categories

Type	THREADED
------	----------

Trade Size

Trade Size	2 INCH
------------	--------

Packaging

Carton	1
Weight Per each	0

Uses, Certifications, and Standards

Approval	UL 6/514B, NEC/CEC
Used On	CONDUIT