



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV4090EL00 4IN PVC Coated Rigid 90

Calpipe Industries, Inc

Catalog Number	PV4090EL00
Manufacturer	Calpipe Industries, Inc
Description	PVC Coated Steel Rigid Conduit Standard Radius Elbow, Standard Radius Type; Steel Material; 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior Finish; UI 6, Cul Approval; Ansi C80.1, Nema RN-1 Applicable Standard; 1 Standard Package
Weight per unit	36.8 (lbs/each)
Product Category	Steel

Features

Applicable Standard	ANSI C80.1, NEMA RN-1
Bend Angle	90 Degree
Bend Radius	16 INCH
End Type	THREADED
Material	Steel

Material, Color, and Finish

Finish	0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior
--------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	Length 21 Inch; Constructional Feature Corrosion Resistant; Application Petrochemical, Water and Wastewater Treatment Facility, Transportation and Infrastructure, Food, Dairy and Beverage, Mining, Marine and Coastal Facility, Chemical Plants, Steel Mills,
Commodity Description	ELBOWS-COUPPLINGS-NIPPLES - STEEL
Description	4IN PVC COATED RIGID 90
extra long description	STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 1 STANDARD PACKAGE; 4 INCH TRADE SIZE; THREADED END TYPE; 90 DEGREE BEND ANGLE; 16 INCH BEND RADIUS; LENGTH 21 INCH; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; APPLICATION PETROCHEMICAL, WATER AND WASTEWATER TREATMENT FACILITY, TRANSPORTATION AND INFRASTRUCTURE, FOOD, DAIRY AND BEVERAGE, MINING, MARINE AND COASTAL FACILITY, CHEMICAL
Long Description	PVC COATED STEEL RIGID CONDUIT STANDARD RADIUS ELBOW, STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 1 STANDARD PACKAGE
Product Type	PVC Coated Steel Rigid Conduit Standard Radius Elbow

Manufacturer Information

Brand	Calpipe Industries, Inc
GTIN	00847656053963
Manufacturers Part Number	PV4090EL00
Model	PV
UPC	847656053963

Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	STANDARD RADIUS

Trade Size

Trade Size	4 INCH
------------	--------

Packaging

Carton	1
Standard Package	1
Weight Per each	36.75

Uses, Certifications, and Standards

Approval	UL 6, CUL
----------	-----------