



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PW301W Pir Wall SWITCH Occ SNSR 120/277V W

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | PW301W |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Wall Switch Occupancy Sensor, Sensor With Relay Type; 1.58 Inch W X 1.39 Inch D X 4.1 Inch H Size; White Finish; UL, Cul Approval; Small Office, Small Conference Room and Lunch/Break Room Application; 120/277 Vac At 50/60 HZ Voltage Rating; Wall Mounting |
| Weight per unit | 0.4700 (lbs/each) |
| Product Category | Lighting Occupancy Sensors |

Features

| | |
|-----------------|--|
| Area Coverage | 35 FT X 30 FT (MAJOR MOTION), 20 FT X 15 FT (MINOR MOTION) |
| Load Rating | 0 to 1000 W at 120 VAC (Ballast/LED/Tungsten), 0 to 1200 W at 277 VAC (Ballast/LED), 1/6 HP at 120/277 VAC |
| Load Type | Ballast/Tungsten/LED |
| Sensor Type | PASSIVE INFRARED |
| Terminal Type | Screw |
| Time Delay | 5/10/15/20/25/30 Min |
| Voltage Rating | 120/277 VAC AT 50/60 HZ |
| Wall Plate Type | DECORATOR |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | white |
|--------|-------|

Dimensions and Weight

| | |
|------|--|
| Size | 1.58 Inch W x 1.39 Inch D x 4.1 Inch H |
|------|--|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|---|
| Additional Information | Sensitivity Adjustment PIR (High/Low) |
| Commodity Description | LIGHTING OCCUPANCY SENSORS |
| Description | PIR WALL SWTCH OCC SNSR 120/277V W |
| extra long description | SENSOR WITH RELAY TYPE; 1.58 INCH W X 1.39 INCH D X 4.1 INCH H SIZE; WHITE FINISH; UL, CUL APPROVAL; SMALL OFFICE, SMALL CONFERENCE ROOM AND LUNCH/BREAK ROOM APPLICATION; 120/277 VAC AT 50/60 HZ VOLTAGE RATING; WALL MOUNTING; SCREW TERMINAL TYPE; 0 TO 1000 W AT 120 VAC (BALLAST/LED/TUNGSTEN), 0 TO 1200 W AT 277 VAC (BALLAST/LED), 1/6 HP AT 120/277 VAC LOAD RATING; DECORATOR WALL PLATE TYPE; PASSIVE INFRARED SENSOR TYPE; 35 FT X 30 FT (MAJOR MOTION), 20 FT X 15 FT (MINOR MOTION) AREA COVERAGE; BALLAST/TUNGS |
| Long Description | WALL SWITCH OCCUPANCY SENSOR, SENSOR WITH RELAY TYPE; 1.58 INCH W X 1.39 INCH D X 4.1 INCH H SIZE; WHITE FINISH; UL, CUL APPROVAL; SMALL OFFICE, SMALL CONFERENCE ROOM AND LUNCH/BREAK ROOM APPLICATION; 120/277 VAC AT 50/60 HZ VOLTAGE RATING; WALL MOUNTING |
| Product Type | Wall Switch Occupancy Sensor |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | Pass & Seymour/Legrand |
| GTIN | 00754182935260 |
| Manufacturers Part Number | PW-301-W |
| UPC | 754182935260 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Miscellaneous residential devices |
| Type | SENSOR WITH RELAY |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 40 |
| Weight Per each | 0.47 |

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | Small Office, Small Conference Room and Lunch/Break Room |
| Approval | UL, CUL |
| Mounting | WALL |