



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QB1020GF Bolt-On Gfci 5MA 1 Pole 10KAIC 20A 120/240V

Eaton Corp

Catalog Number	QB1020GF
Manufacturer	Eaton Corp
Description	Eaton QB Gfci Circuit Breaker, Ground Fault Circuit Breaker, 20A, 10 Kaic, Single-Pole, 120/240V, Non-Interchangeable, 5 Ma Trip Sensitivity, Bolt-On, #14-4 Awg, QB
Weight per unit	0.5000 (lbs/each)
Product Category	On Circuit Breakers

Features

connection	BOLT-ON
dimensions	4.0000 IN X 3.5000 IN X 1.0000 IN
interrupt rating	10
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	BOLT-ON GFCI 5MA 1 POLE 10KAIC 20A 120/240V
extra long description	ETN QB1020GF Bolt-on GFCI, 1 pole,
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton QB GFCI circuit breaker,Ground fault circuit breaker,20A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,Bolt-on,#14-4 AWG,QB
Product Type	Bolt-On Gfci, 1 Pole, 10KAIC, 20a

Manufacturer Information

Brand	Eaton
GTIN	00786680222498
Manufacturers Part Number	QB1020GF
UPC	786680222498

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	GFCI circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	20
Weight Per each	0.5

Uses, Certifications, and Standards

Application	Marine Vessels and Equipment - Marine Vessels and Equipment - OtherOtherGeneration - Renewable Energy - Alternative EnergyGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedCommercial / Institutional Buildings / Structures - Power Distribution and Controls
standard	UL 489,Contact Manufacturer