

Specifications



Eaton PVML-7-3TW-UNV1

Eaton Crouse-Hinds series Champ Pro PVML LED fixture, Cool white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 129 lm/W, Die cast aluminum, Wall mount, Type V, 1" trade size, 100-277 Vac, 127-250 Vdc, 57W

Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Champ Pro PVML LED light fixture
CATALOG NUMBER	PVML-7-3TW-UNV1
UPC	662276881020
PRODUCT LENGTH/DEPTH	13.96 in
PRODUCT HEIGHT	11.31 in
PRODUCT WIDTH	11.62 in
PRODUCT WEIGHT	23.5 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC IEC
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	7000
LUMENS PER WATT	129
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Wall
TRADE SIZE	1"
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	57W
DIMMING	Dimmable driver
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	175W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

Resources

3D MODELS	SP3D Design Package - Champ Pro PVML Industrial LED Light Fixtures
BROCHURES	Crouse-Hinds series DLC approved lighting products Crouse-Hinds series Global LED lighting portfolio Crouse-Hinds series Champ Pro PVML LED Luminaires - 3,000 to 13,000 lumens brochure Crouse-Hinds series industrial LED lighting solutions
CATALOGS	Crouse-Hinds series Champ Pro PVML LED luminaires - 3,000 to 13,000 lumens catalog page
CERTIFICATION REPORTS	Champ Pro PVML Industrial LED Light Fixtures Canadian certification Champ Pro PVML Industrial LED Light Fixtures UL certification EC Declaration of Conformity - Crouse-Hinds series Champ Pro PVML LED Luminaires
INSTALLATION INSTRUCTIONS	IF 1888 - Champ VMVL and PVML Driver Replacement IF 1882 - Champ VMVL and PVML LED luminaires
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - PVML-7-3TW-UNV1 Champ Pro PVM Industrial LED

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.