

# Specifications

## Eaton QBHGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Two-pole, 120/240V, QBHGF



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBHGFT2020
<b>UPC</b>	786676027823
<b>PRODUCT LENGTH/DEPTH</b>	4.5 in
<b>PRODUCT HEIGHT</b>	2 in
<b>PRODUCT WIDTH</b>	2.75 in
<b>PRODUCT WEIGHT</b>	0.6 lb
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	HACR rated

## Physical Attributes

CIRCUIT BREAKER TYPE	QBHGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

## Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	22 kAIC
VOLTAGE RATING	120/240 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBHGFT2020</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton QBHGFT2020

Eaton QB GFCI circuit breaker, Ground fault circuit breaker, 20A, 22 kAIC, Two-pole, 120/240V, QBHGF



Photo is representative



### General specifications

<b>PRODUCT NAME</b>	Eaton QB GFCI circuit breaker
<b>CATALOG NUMBER</b>	QBHGFT2020
<b>UPC</b>	786676027823
<b>PRODUCT LENGTH/DEPTH</b>	4.5 in
<b>PRODUCT HEIGHT</b>	2 in
<b>PRODUCT WIDTH</b>	2.75 in
<b>PRODUCT WEIGHT</b>	0.6 lb
<b>CERTIFICATIONS</b>	UL 489
<b>CATALOG NOTES</b>	HACR rated

## Physical Attributes

CIRCUIT BREAKER TYPE	QBHGF
NUMBER OF POLES	Two-pole
TYPE	Ground fault circuit breaker

## Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	22 kAIC
VOLTAGE RATING	120/240 V

## Resources

SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - QBHGFT2020</a>
-------------------------------	--

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

