

# Eaton R5A3025U

Catalog Number: R5A3025U

Eaton rotary disconnect switch, 25 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton rotary disconnect switch	R5A3025U
<b>UPC</b>	<b>Product Length/Depth</b>
786685402864	2.57 in
<b>Product Height</b>	<b>Product Width</b>
3.35 in	1.77 in
<b>Product Weight</b>	<b>Warranty</b>
0.5 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Compliances</b>	<b>Certifications</b>
CCC Marked	CSA Certified
	UL 508
	IEC Rated
	EN Listed

## Catalog Notes

Suitable as motor disconnect

## defaultTaxonomyAttributeLabel

### Amperage Rating

25A

### Product Category

Rotary Switch

### Voltage rating

600 V

### Series

R5

### Fuse configuration

Non-fusible

### Number of poles

Three-pole

## Resources

### Brochures

Pringle Switches - Bolted contact switches

### Catalogs

Eaton's Volume 2—Commercial Distribution

### Drawings

R5A30\_U 2D Drawing Xchange

R5A30\_U 2D PDF

R5A30\_U AutoCAD 2D Footprint

R5A30\_U 3D Model Xchange

R5A30\_U 3D Inventor

R5A30\_U AutoCAD 2D Footprint (mm)

### Multimedia

Switching Devices Flex Center

### Specifications and datasheets

Eaton Specification Sheet - R5A3025U



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

# Eaton R5A3025U

Catalog Number: R5A3025U

Eaton rotary disconnect switch, 25 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton rotary disconnect switch	R5A3025U
<b>UPC</b>	<b>Product Length/Depth</b>
786685402864	2.57 in
<b>Product Height</b>	<b>Product Width</b>
3.35 in	1.77 in
<b>Product Weight</b>	<b>Warranty</b>
0.5 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Compliances</b>	<b>Certifications</b>
CCC Marked	CSA Certified
	UL 508
	IEC Rated
	EN Listed

## Catalog Notes

Suitable as motor disconnect

## defaultTaxonomyAttributeLabel

### Amperage Rating

25A

### Product Category

Rotary Switch

### Voltage rating

600 V

### Series

R5

### Fuse configuration

Non-fusible

### Number of poles

Three-pole

## Resources

### Brochures

Pringle Switches - Bolted contact switches

### Catalogs

Eaton's Volume 2—Commercial Distribution

### Drawings

R5A30\_U 2D Drawing Xchange

R5A30\_U 2D PDF

R5A30\_U AutoCAD 2D Footprint

R5A30\_U 3D Model Xchange

R5A30\_U 3D Inventor

R5A30\_U AutoCAD 2D Footprint (mm)

### Multimedia

Switching Devices Flex Center

### Specifications and datasheets

Eaton Specification Sheet - R5A3025U



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia