

Eaton R5A3040U

Catalog Number: R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V



General specifications

Product Name

Eaton rotary disconnect switch

Catalog Number

R5A3040U

UPC

786685402888

Product Length/Depth

2.57 in

Product Height

3.35 in

Product Width

1.77 in

Product Weight

0.5 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CCC Marked

Certifications

CSA Certified

EN Listed

IEC Rated

UL 508

Catalog Notes

Suitable as motor disconnect

Physical Attributes

Number of poles

Three-pole

Series

R5

Performance Ratings

Amperage Rating

40A

Voltage rating

600 V

Miscellaneous

Product Category

Rotary Switch

Resources

Brochures

Pringle Switches - Bolted contact switches

Catalogs

Eaton's Volume 2—Commercial Distribution

Drawings

R5A30_U 2D Drawing Xchange

R5A30_U 3D Inventor

R5A30_U AutoCAD 2D Footprint

R5A30_U 3D Model Xchange

R5A30_U 2D PDF

R5A30_U AutoCAD 2D Footprint (mm)

Multimedia

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - R5A3040U



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton R5A3040U

Catalog Number: R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V



General specifications

Product Name

Eaton rotary disconnect switch

Catalog Number

R5A3040U

UPC

786685402888

Product Length/Depth

2.57 in

Product Height

3.35 in

Product Width

1.77 in

Product Weight

0.5 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CCC Marked

Certifications

CSA Certified

EN Listed

IEC Rated

UL 508

Catalog Notes

Suitable as motor disconnect

Physical Attributes

Number of poles

Three-pole

Series

R5

Performance Ratings

Amperage Rating

40A

Voltage rating

600 V

Miscellaneous

Product Category

Rotary Switch

Resources

Brochures

Pringle Switches - Bolted contact switches

Catalogs

Eaton's Volume 2—Commercial Distribution

Drawings

R5A30_U 2D Drawing Xchange

R5A30_U 3D Inventor

R5A30_U AutoCAD 2D Footprint

R5A30_U 3D Model Xchange

R5A30_U 2D PDF

R5A30_U AutoCAD 2D Footprint (mm)

Multimedia

Switching Devices Flex Center

Specifications and datasheets

Eaton Specification Sheet - R5A3040U



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia