

Eaton R9C3100U

Catalog Number: R9C3100U

Eaton rotary disconnect switch, 100 A, Non-fusible, Three-pole, Switch body, R9 Series, 600 V, C frame



Photo is representative

General specifications

Product Name	Catalog Number
Eaton rotary disconnect switch	R9C3100U
UPC	Product Length/Depth
786685402932	2.52 in
Product Height	Product Width
5.62 in	3.07 in
Product Weight	Warranty
0.5 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CSA Certified
EN Listed
IEC Rated
UL 98

defaultTaxonomyAttributeLabel

Amperage Rating

100A

Product Category

Switch Body

Voltage rating

600 V

Series

R9

Fuse configuration

Non-fusible

Number of poles

Three-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[R9C3_U AutoCAD 2D Footprint](#)

[R9C3_U 3D Model Xchange](#)

[R9C3_U 2D PDF](#)

[R9C3_U 3D Inventor](#)

[R9C3_U AutoCAD 2D Footprint \(mm\)](#)

[R9C3_U 2D Drawing Xchange](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - R9C3100U](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton R9C3100U

Catalog Number: R9C3100U

Eaton rotary disconnect switch, 100 A, Non-fusible, Three-pole, Switch body, R9 Series, 600 V, C frame



Photo is representative

General specifications

Product Name

Eaton rotary disconnect switch

Catalog Number

R9C3100U

UPC

786685402932

Product Length/Depth

2.52 in

Product Height

5.62 in

Product Width

3.07 in

Product Weight

0.5 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

CSA Certified

EN Listed

IEC Rated

UL 98

defaultTaxonomyAttributeLabel

Amperage Rating

100A

Product Category

Switch Body

Voltage rating

600 V

Series

R9

Fuse configuration

Non-fusible

Number of poles

Three-pole

Resources

Catalogs

[Eaton's Volume 5—Motor Control and Protection](#)

Drawings

[R9C3_U AutoCAD 2D Footprint](#)

[R9C3_U 3D Model Xchange](#)

[R9C3_U 2D PDF](#)

[R9C3_U 3D Inventor](#)

[R9C3_U AutoCAD 2D Footprint \(mm\)](#)

[R9C3_U 2D Drawing Xchange](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - R9C3100U](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)