

**Greater lighting control in a single, space-saving device.**

RCD11, RCD113, RCD33, RCD38TR


Aesthetically improved yet reliable as ever, these combination switches give end users greater lighting control by combining multiple functions in a one-gang configuration. Transform any of these devices into an illuminated switch in seconds with our Snap-In Light Module (RCDLM, sold separately). These combination switches are ideal for residential, multi-dwelling, commercial office and hospitality applications, and as part of the radiant® collection, now offer a better fit, form and finish.

## Features & Benefits

**Full wraparound metal strap**, commercial grade with lock-in tabs.

**All screws are tri-drive.**

**External screw-pressure-plate back and side wired.** Accepts #14 - #10 AWG.



**Snap-In Light Module** (sold separately)  
 White LED locator light glows when device is off for easy location in the dark.

**Unique "Up/Down" switches** match the look and feel of standard paddle switches.

**Easy-to-use oversized main switch** for primary load.

**Impact-resistant face and body.**

**RCD113W**

- Part of the radiant® collection
- Patented shutter system—now with black "invisi-shutters" for an invisible effect preferred by end users—helps prevent improper insertion of foreign objects (RCD38TR only).
- Single Pole/3-Way Switches can be wired as a single pole or 3-way switch.

- Patented split-circuit tab – easily accessible and can be reinstalled without a tool.

**Snap-In Light Module:**

- Lights when OFF.
- Uses energy-efficient LED light.
- LED light will not generate heat and will last, on average, 47 years.

## 3rd Party Compliance

 cULus Listed, UL20, Conform to NEMA WD-1 and WD-6

## Technical Information


### Performance

#### Electrical

Supply Voltage 120/125VAC

#### Environmental

Application Indoor Use Only



**RCD113W**

### Warranty

One year

## Ordering Information

### Two Single Pole Switches

Catalog Number	Rating			3rd Party Compliance	
	A	VAC	Color	UL20	cULus
RCD11I	15	120/125	Ivory	•	•
RCD11W	15	120/125	White	•	•
RCD11BK	15	120/125	Black	•	•
RCD11LA	15	120/125	Light Almond	•	•

### Two Single Pole/3-Way Switches

RCD33I	15	120/125	Ivory	•	•
RCD33W	15	120/125	White	•	•
RCD33BK	15	120/125	Black	•	•
RCD33LA	15	120/125	Light Almond	•	•

### Two Single Pole Switches & One Single Pole/3-Way Switch

RCD113I	15	120/125	Ivory	•	•
RCD113W	15	120/125	White	•	•
RCD113BK	15	120/125	Black	•	•
RCD113LA	15	120/125	Light Almond	•	•



### Single Pole/3-Way Switch & Tamper-Resistant Receptacle

Catalog Number	Rating			NEMA Config. No.	3rd Party Compliance		
	A	VAC	Color		UL20	UL498	cULus
RCD38TRI	15	120/125	Ivory	5-15R	•	•	•
RCD38TRW	15	120/125	White	5-15R	•	•	•
RCD38TRBK	15	120/125	Black	5-15R	•	•	•
RCD38TRLA	15	120/125	Light Almond	5-15R	•	•	•

## Features

- Module simply snaps-in for easy installation.

#### Snap-In Light Module:

- Lights when OFF.
- Uses energy-efficient LED light.
- LED light will not generate heat and will last, on average, 47 years.


#### radiant® Locator Light Module

Catalog Number	Rating			3rd Party Compliance
	A	VAC	Color	cULus
RCDLM	15	120/125	Clear	•



RCDLM

#### Adding a Snap-In Light Module



---

## Vertical Markets


- Residential
- Multiple Dwelling
- Hospitality/Lodging

---

## Also available in the radiant® collection

- GFCI Receptacles
- Tamper-Resistant and Standard Duplex Receptacles
- Paddle Switches
- Lighting & Fan Controls
- Sensors
- Timers
- Home Automation Controls
- USB Charging Devices
- Night Lights
- Screwless Wall Plates

---

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.




**Legrand, North America**  
60 Woodlawn Street  
West Hartford, CT 06110  
1.877.BY.LEGRAND (295.3472)  
[www.legrand.us](http://www.legrand.us)

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

FOLLOW US





**Greater lighting control in a single, space-saving device.**

RCD11, RCD113, RCD33, RCD38TR


Aesthetically improved yet reliable as ever, these combination switches give end users greater lighting control by combining multiple functions in a one-gang configuration. Transform any of these devices into an illuminated switch in seconds with our Snap-In Light Module (RCDLM, sold separately). These combination switches are ideal for residential, multi-dwelling, commercial office and hospitality applications, and as part of the radiant® collection, now offer a better fit, form and finish.

## Features & Benefits

**Full wraparound metal strap**, commercial grade with lock-in tabs.

**All screws are tri-drive.**

**External screw-pressure-plate back and side wired.** Accepts #14 - #10 AWG.



**Snap-In Light Module** (sold separately)  
 White LED locator light glows when device is off for easy location in the dark.

**Unique "Up/Down" switches** match the look and feel of standard paddle switches.

**Easy-to-use oversized main switch** for primary load.

**Impact-resistant face and body.**

**RCD113W**

- Part of the radiant® collection
- Patented shutter system—now with black "invisi-shutters" for an invisible effect preferred by end users—helps prevent improper insertion of foreign objects (RCD38TR only).
- Single Pole/3-Way Switches can be wired as a single pole or 3-way switch.

- Patented split-circuit tab – easily accessible and can be reinstalled without a tool.

**Snap-In Light Module:**

- Lights when OFF.
- Uses energy-efficient LED light.
- LED light will not generate heat and will last, on average, 47 years.

## 3rd Party Compliance

 cULus Listed, UL20, Conform to NEMA WD-1 and WD-6

## Technical Information


### Performance

#### Electrical

Supply Voltage 120/125VAC

#### Environmental

Application Indoor Use Only



**RCD113W**

### Warranty

One year

## Ordering Information

### Two Single Pole Switches

Catalog Number	Rating			3rd Party Compliance	
	A	VAC	Color	UL20	cULus
RCD11I	15	120/125	Ivory	•	•
RCD11W	15	120/125	White	•	•
RCD11BK	15	120/125	Black	•	•
RCD11LA	15	120/125	Light Almond	•	•

### Two Single Pole/3-Way Switches

RCD33I	15	120/125	Ivory	•	•
RCD33W	15	120/125	White	•	•
RCD33BK	15	120/125	Black	•	•
RCD33LA	15	120/125	Light Almond	•	•

### Two Single Pole Switches & One Single Pole/3-Way Switch

RCD113I	15	120/125	Ivory	•	•
RCD113W	15	120/125	White	•	•
RCD113BK	15	120/125	Black	•	•
RCD113LA	15	120/125	Light Almond	•	•



### Single Pole/3-Way Switch & Tamper-Resistant Receptacle

Catalog Number	Rating			NEMA Config. No.	3rd Party Compliance		
	A	VAC	Color		UL20	UL498	cULus
RCD38TRI	15	120/125	Ivory	5-15R	•	•	•
RCD38TRW	15	120/125	White	5-15R	•	•	•
RCD38TRBK	15	120/125	Black	5-15R	•	•	•
RCD38TRLA	15	120/125	Light Almond	5-15R	•	•	•

## Features

- Module simply snaps-in for easy installation.

#### Snap-In Light Module:


- Lights when OFF.
- Uses energy-efficient LED light.
- LED light will not generate heat and will last, on average, 47 years.

#### radiant® Locator Light Module

Catalog Number	Rating			3rd Party Compliance
	A	VAC	Color	cULus
RCDLM	15	120/125	Clear	•



RCDLM



Adding a Snap-In Light Module



---

## Vertical Markets


- Residential
- Multiple Dwelling
- Hospitality/Lodging

---

## Also available in the radiant® collection

- GFCI Receptacles
- Tamper-Resistant and Standard Duplex Receptacles
- Paddle Switches
- Lighting & Fan Controls
- Sensors
- Timers
- Home Automation Controls
- USB Charging Devices
- Night Lights
- Screwless Wall Plates

---

 The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act compliant. 100% of the electricity used to manufacture Flo sheets is generated with Green-e certified renewable energy.

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



**Legrand, North America**  
60 Woodlawn Street  
West Hartford, CT 06110  
1.877.BY.LEGRAND (295.3472)  
[www.legrand.us](http://www.legrand.us)

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
905.738.9195  
[www.legrand.ca](http://www.legrand.ca)

FOLLOW US

