

Eaton REN-30

Catalog Number: REN-30

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 30 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications



Product Name	Catalog Number
Eaton Bussmann series REN fuse	REN-30
UPC	Product Length/Depth
051712100304	2 in
Product Height	Product Width
0.56 in	0.56 in
Product Weight	Warranty
0.55 lb	Not Applicable
Compliances	
Not Applicable	

Electrical rating

Amperage Rating

30 A

Interrupt rating

10 kAIC

Voltage rating

250 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[REN-30~SUPER LAG RENEWABLE FUSE 30/250](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - REN-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton REN-30

Catalog Number: REN-30

Eaton Bussmann series REN fuse, time lag, non current-limiting, Industrial and commercial structures, 30 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC, Standard, 10, 250 V

General specifications



Product Name	Catalog Number
Eaton Bussmann series REN fuse	REN-30
UPC	Product Length/Depth
051712100304	2 in
Product Height	Product Width
0.56 in	0.56 in
Product Weight	Warranty
0.55 lb	Not Applicable
Compliances	
Not Applicable	

Electrical rating

Amperage Rating

30 A

Interrupt rating

10 kAIC

Voltage rating

250 V

Physical details

Packaging type

Standard

General information

Class

Class H

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Quantity

10

Special features

Super lag, time lag, non current-limiting

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[REN-30~SUPER LAG RENEWABLE FUSE 30/250](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - REN-30](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia