

Specifications

Eaton RES-60

Eaton Bussmann series RES fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Standard, 10, 600 V



General specifications

PRODUCT NAME	Eaton Bussmann series RES fuse
CATALOG NUMBER	RES-60
UPC	051712110600
EAN	5027590465991
PRODUCT LENGTH/DEPTH	0.78 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	0.78 in
PRODUCT WEIGHT	0.29 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	60 A
INTERRUPT RATING	10 kAIC at 250 Vac
VOLTAGE RATING	600 V

General information

CLASS	Class H
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
QUANTITY	10
SPECIAL FEATURES	Super lag, time lag, non current-limiting

Physical details

PACKAGING TYPE	Standard
----------------	----------

Resources

	Bussmann series complete full line catalog no. 1007
CATALOGS	RES-60~SUPER LAG RENEWABLE FUSE 60/600 Edison full line catalog 1005
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - RES-60

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton RES-60

Eaton Bussmann series RES fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Standard, 10, 600 V



General specifications

PRODUCT NAME	Eaton Bussmann series RES fuse
CATALOG NUMBER	RES-60
UPC	051712110600
EAN	5027590465991
PRODUCT LENGTH/DEPTH	0.78 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	0.78 in
PRODUCT WEIGHT	0.29 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable



Powering Business Worldwide

Electrical rating

AMPERAGE RATING	60 A
INTERRUPT RATING	10 kAIC at 250 Vac
VOLTAGE RATING	600 V

General information

CLASS	Class H
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
QUANTITY	10
SPECIAL FEATURES	Super lag, time lag, non current-limiting

Physical details

PACKAGING TYPE	Standard
----------------	----------

Resources

	Bussmann series complete full line catalog no. 1007
CATALOGS	RES-60~SUPER LAG RENEWABLE FUSE 60/600 Edison full line catalog 1005
MULTIMEDIA	Bussmann series Fuseology
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - RES-60

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

