



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RF9640NDLA Z-Wave Plus Dimmer 300W Light Almod

*Eaton Wiring Devices*

Catalog Number	RF9640NDLA
Manufacturer	Eaton Wiring Devices
Description	Eaton Z-Wave Plus Dimmer Switch, Light Almond, Single Pole, 120 Vac, 300W Dimmable Led/CFL, 600W Incandescent, Halogen, Magnetic Low Voltage, Electronic Low Voltage, Dimmer Switch, Multi-Location, 32°F to 104°F (0°C to 40°C) 757228
Weight per unit	0.3700 (lbs/each)
Product Category	Lighting Dimmers

### Features

dimensions	1.4200 IN X 1.8000 IN X 4.2000 IN
media	Yes
Voltage Rating	120 V
Wattage	300 W (LED, CFL), 600 W (INC/HAL, ELV, MLV)

### Descriptions

Description	Z-WAVE PLUS DIMMER 300W LIGHT ALMOD
extra long description	EWD RF9640-NDLA Z-Wave Plus Dimmer
Features	Eaton's complete offering of wireless lighting controls are easy to install, require no special wiring and are perfect for both new construction and existing homes. With our Z-Wave Plus wireless collection you get enhanced cybersecurity, improved wireless performance and flexibility to choose from 10 different colors to match your lighting mood and room decor.
Long Description	Eaton Z-Wave plus dimmer switch, Light almond, Single pole, 120 Vac, 300W Dimmable LED/CFL, 600W Incandescent, Halogen, Magnetic Low Voltage, Electronic Low Voltage, Dimmer switch, Multi-location, 32°F to 104°F (0°C to 40°C) 757228
Product Type	Z-Wave Plus Dimmer 300W Light Almod
Special Features	Dimmers

### Manufacturer Information

Brand	Eaton
GTIN	00032664757228
Manufacturers Part Number	RF9640-NDLA
UPC	032664757228

### Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Dimmer switch



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	6
Weight Per each	0.37

## Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
Operating Temperature standard	32 to 104 °F (0 to 40 °C) cULus Listed,NOM