

# Specifications

## Eaton RDCH42B200I



Photo is representative

Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit, Main circuit breaker, 200 A, Retro size group d, Cover height: 47 in, Cover width: 24 in, NEMA 1, 25 kAIC, CH, Surface, flush, 42 Circuits, Single-phase, 0.75 in, #1 AWG-300 kcmil

### General specifications

<b>PRODUCT NAME</b>	Eaton CH retrofit kit
<b>CATALOG NUMBER</b>	RDCH42B200I
<b>UPC</b>	786685211114
<b>PRODUCT LENGTH/DEPTH</b>	6 in
<b>PRODUCT HEIGHT</b>	45 in
<b>PRODUCT WIDTH</b>	22 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 67
<b>CATALOG NOTES</b>	Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.



### Product specifications

**TYPE** Retrofit kit

### Resources

**MULTIMEDIA** [AFCI Educational Video](#)

<b>AMPERAGE RATING</b>	200 A
<b>MAIN CIRCUIT BREAKER</b>	CH
<b>MOUNTING</b>	Surface, flush
<b>NUMBER OF CIRCUITS</b>	42
<b>PHASE</b>	Single-phase
<b>WIRE SIZE</b>	#1 AWG-300 kcmil
<b>BOX SIZE</b>	Retro size group d
<b>COVER HEIGHT</b>	47
<b>COVER WIDTH</b>	24
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	25 kAIC

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - RDCH42B200I</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



# Specifications

## Eaton RDCH42B200I



Photo is representative

Eaton CH 3/4-inch Loadcenter Retrofit Stocking Kit, Main circuit breaker, 200 A, Retro size group d, Cover height: 47 in, Cover width: 24 in, NEMA 1, 25 kAIC, CH, Surface, flush, 42 Circuits, Single-phase, 0.75 in, #1 AWG-300 kcmil

### General specifications

<b>PRODUCT NAME</b>	Eaton CH retrofit kit
<b>CATALOG NUMBER</b>	RDCH42B200I
<b>UPC</b>	786685211114
<b>PRODUCT LENGTH/DEPTH</b>	6 in
<b>PRODUCT HEIGHT</b>	45 in
<b>PRODUCT WIDTH</b>	22 in
<b>PRODUCT WEIGHT</b>	1 lb
<b>WARRANTY</b>	1 year
<b>CERTIFICATIONS</b>	UL 67
<b>CATALOG NOTES</b>	Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.



### Product specifications

**TYPE** Retrofit kit

### Resources

**MULTIMEDIA** [AFCI Educational Video](#)

<b>AMPERAGE RATING</b>	200 A
<b>MAIN CIRCUIT BREAKER</b>	CH
<b>MOUNTING</b>	Surface, flush
<b>NUMBER OF CIRCUITS</b>	42
<b>PHASE</b>	Single-phase
<b>WIRE SIZE</b>	#1 AWG-300 kcmil
<b>BOX SIZE</b>	Retro size group d
<b>COVER HEIGHT</b>	47
<b>COVER WIDTH</b>	24
<b>ENCLOSURE</b>	NEMA 1
<b>INTERRUPT RATING</b>	25 kAIC

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - RDCH42B200I</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type CH circuit breaker limited warranty June 2024</a>

<b>PROJECT NAME:</b>
<b>PROJECT NUMBER:</b>
<b>PREPARED BY:</b>
<b>DATE:</b>



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

