

# Eaton RES-60

Catalog Number: RES-60

Eaton Bussmann series RES fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Standard, 10, 600 V

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series RES fuse	RES-60
<b>UPC</b>	<b>EAN</b>
051712110600	5027590465991
<b>Product Length/Depth</b>	<b>Product Height</b>
0.78 in	5.5 in
<b>Product Width</b>	<b>Product Weight</b>
0.78 in	0.29 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	Not Applicable

## Electrical rating

### Amperage Rating

60 A

### Interrupt rating

10 kAIC at 250 Vac

### Voltage rating

600 V

## Physical details

### Packaging type

Standard

## General information

### Class

Class H

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Quantity

10

### Special features

Super lag, time lag, non current-limiting

## Resources

### Catalogs

[Edison full line catalog 1005](#)

[Bussmann series complete full line catalog no. 1007](#)

[RES-60~SUPER LAG RENEWABLE FUSE 60/600](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - RES-60](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton RES-60

Catalog Number: RES-60

Eaton Bussmann series RES fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Standard, 10, 600 V

## General specifications



<b>Product Name</b>	<b>Catalog Number</b>
Eaton Bussmann series RES fuse	RES-60
<b>UPC</b>	<b>EAN</b>
051712110600	5027590465991
<b>Product Length/Depth</b>	<b>Product Height</b>
0.78 in	5.5 in
<b>Product Width</b>	<b>Product Weight</b>
0.78 in	0.29 lb
<b>Warranty</b>	<b>Compliances</b>
Not Applicable	Not Applicable

## Electrical rating

### Amperage Rating

60 A

### Interrupt rating

10 kAIC at 250 Vac

### Voltage rating

600 V

## Physical details

### Packaging type

Standard

## General information

### Class

Class H

### Connection

Ferrule end x ferrule end

### Fuse indicator

Non-indicating

### Quantity

10

### Special features

Super lag, time lag, non current-limiting

## Resources

### Catalogs

[Edison full line catalog 1005](#)

[Bussmann series complete full line catalog no. 1007](#)

[RES-60~SUPER LAG RENEWABLE FUSE 60/600](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - RES-60](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)