



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

S11905 4W T5 Mini Led Lamp 4000K

Satco

| | |
|------------------|---|
| Catalog Number | S11905 |
| Manufacturer | Satco |
| Description | 4 Watt T5 Led - Miniature Bi-Pin Base - 4000K - 50000 Average Rated Hours - 400 Lumens - 120-277 Volts |
| Weight per unit | 0.0800 (lbs/each) |
| Product Category | Shape & Circular Lamps |

Features

| | |
|----------------|--|
| average life | 50000 |
| Base | Miniature Bi Pin |
| beam angle | 240 |
| dimnable | No |
| lumens | 400 |
| Material | Glass |
| Shape | T5 |
| Voltage Rating | 277 |
| Warranty | 5 Year Limited - T5 LED Bulbs - Ballast Bypass |
| Wattage | 4 |

Material, Color, and Finish

| | |
|-------------------|------|
| color temperature | 4000 |
|-------------------|------|

Dimensions and Weight

| | |
|----------|-------|
| Diameter | 0.63 |
| Length | 11.91 |

Descriptions

| | |
|------------------------|---|
| Description | 4W T5 MINI LED LAMP 4000K |
| extra long description | SATCO S11905 4W/LED/T5/840/BP |
| Long Description | 4 Watt T5 LED - Miniature Bi-pin Base - 4000K - 50000 Average Rated Hours - 400 Lumens - 120-277 Volts |
| Product Type | 4W/Led/T5/840/BP |
| Special Features | Warranty: 5 Year Limited; Country of origin: China; ANSI base: G5; Ballast bypass direct: Ballast Bypass; CEC: Lawful for sale in California; Color temperature: Cool White; Fluorescent equivalence: 8 watts; Lamp appearance: Frosted; Lamp type: T5; Lamp ballast type: Type B; Lamp end type: Double ended; Lens finish: Frosted; Lens material: Glass; Operating frequency: 50/60Hz; ROHS compliant: Yes; Safety listing: cULus Classified - Damp; Shatterproof: Yes; Voltage range: 120-277V |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923119057 |
| Manufacturers Part Number | S11905 |
| UPC | 045923119057 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------------|
| Category Description | Fuses & Fuse Accessories |
| Type | LED T5 |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight | 0.08 |
| Weight Per each | 0.08 |

Uses, Certifications, and Standards

| | |
|-----------------------|--|
| Operating Temperature | -25C (-13F) to a maximum of +45C (+113F) |
|-----------------------|--|