



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **S14120TLO 14-1/2" 120LB WR NylN HD BLK CBL Tie** *Panduit Corporation*

Catalog Number	S14120TLO
Manufacturer	Panduit Corporation
Description	The S14-120-TLO Stronghold Cable Ties Offers Contractors An Economical Cable Tie Option For Commercial Construction and General-Purpose Applications. Light-Heavy, 14.49" (368MM) Length and Are Ah-2 Plenum Rated. For Outdoor Use, Made Of Weather Resistant Nylon 6.6, Are Black In Color and Come In Packages Of 250.
Weight per unit	0.0103 (lbs/each)
Product Category	Cable Ties & Wraps

### **Features**

media	Yes
Tensile Strength	120

### **Dimensions and Weight**

Length	14.49
Width	0.49

### **Descriptions**

Description	14-1/2" 120LB WR NYL N HD BLK CBL TIE
extra long description	PAN S14-120-TLO StrongHold™ S14-120
Long Description	The S14-120-TLO StrongHold Cable Ties offers contractors an economical cable tie option for commercial construction and general-purpose applications. Light-heavy, 14.49" (368mm) length and are AH-2 Plenum rated. For outdoor use, made of Weather Resistant Nylon 6.6, are black in color and come in packages of 250.
Product Type	Stronghold™ S14-120-TLO Cable Tie, Black, Pa 6.6, 120LB Min
Special Features	Plenum

### **Manufacturer Information**

Brand	PANDUIT
GTIN	00613056340671
Manufacturers Part Number	S14-120-TLO
UPC	613056340671

### **Taxonomies, Classifications, and Categories**

Category Description	Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps
Type	Cable Tie



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

minimum qty ..... 250 .....

## Packaging

Carton ..... 250 .....

Package ..... 2500 .....

Weight Per each ..... 0.01034 .....

## Uses, Certifications, and Standards

standard ..... UL 62275 Compliant (Type 2, 21), RoHS Compliant .....