



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S10N04A82N .10KVA Buck Boost Transformer 1PH 120X240-12/24V

Eaton Corp

| | |
|------------------|--|
| Catalog Number | S10N04A82N |
| Manufacturer | Eaton Corp |
| Description | Eaton General Purpose Encapsulated Transformer, Buck-Boost General-Purpose Encapsulated Transformer, Ep, Aluminum, Nema 3R, 54, 60 HZ, Single-Phase, 120 V, 240 V, 12/24 V, None, 115 °C Rise, 0.1 Kva, Indoor-Outdoor, 3B |
| Weight per unit | 8.6 (lbs/each) |
| Product Category | 20021107100233 |

Features

| | |
|-------------------|-----------------------------------|
| connection | 3B |
| design | EP |
| dimensions | 4.0000 IN X 4.1100 IN X 8.5000 IN |
| frame | 54 |
| Number of Phases | Single-phase |
| Primary Voltage | 120 V, 240 V |
| Secondary Voltage | 12/24 V |

Descriptions

| | |
|------------------------|---|
| Description | .10KVA BUCK BOOST TRANSFORMER 1PH 120X240-12/24V |
| extra long description | ETN S10N04A82N .10KVA Buck Boost TX |
| Features | Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA. |
| Long Description | Eaton General purpose encapsulated transformer, buck-boost general-purpose encapsulated transformer, EP, aluminum, NEMA 3R, 54, 60 Hz, single-phase, 120 V, 240 V, 12/24 V, NONE, 115 °C rise, 0.1 KVA, indoor-outdoor, 3B |
| Product Type | .10KVA Buck Boost TX 1PH 120X240-12/24V |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Eaton |
| GTIN | 00786680383106 |
| Manufacturers Part Number | S10N04A82N |
| UPC | 786680383106 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description.....BUCK & BOOST TRANSFORMERS

Type.....Encapsulated transformer

Packaging

Carton.....1

Weight Per each.....8.58

Uses, Certifications, and Standards

Application.....Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels
and EOEMs

Frequency Rating.....60 Hz

standard.....UL Listed

Temperature Rating.....115 °C rise