



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **S10N06P16P 1.5KVA Buck Boost Transformer 1PH 120X240-16/32V**

*Eaton Corp*

Catalog Number	S10N06P16P
Manufacturer	Eaton Corp
Description	Eaton General Purpose Encapsulated Transformer, Ep, Aluminum, Nema 3R, 67P, 60 HZ, Single-Phase, 120 V, 240 V, 16/32 V, None, 115 °C Rise, 1.5 Kva, Indoor-Outdoor, 3C
Weight per unit	1.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

### **Features**

connection	3C
design	EP
dimensions	6.5600 IN X 5.5300 IN X 13.0300 IN
frame	67P
Number of Phases	Single-phase
Primary Voltage	120 V, 240 V
Secondary Voltage	16/32 V

### **Descriptions**

Description	1.5KVA BUCK BOOST TRANSFORMER 1PH 120X240-16/32V
extra long description	ETN S10N06P16P 1.5KVA BUCK BOOST TX
Features	Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA.
Long Description	Eaton General purpose encapsulated transformer, EP, aluminum, NEMA 3R, 67P, 60 Hz, single-phase, 120 V, 240 V, 16/32 V, NONE, 115 °C rise, 1.5 KVA, indoor-outdoor, 3C
Product Type	1.5KVA Buck Boost TX 1PH 120X240-16/32V

### **Manufacturer Information**

Brand	Eaton
GTIN	00786680073632
Manufacturers Part Number	S10N06P16P
UPC	786680073632



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description.....BUCK & BOOST TRANSFORMERS

Type.....Encapsulated transformer

## Packaging

Carton.....1

Weight Per each.....1

## Uses, Certifications, and Standards

Application.....Commercial / Institutional Buildings / Structures - Commercial /  
Institutional Buildings / Structures - Other

Frequency Rating.....60 Hz

standard.....UL Listed

Temperature Rating.....115 °C rise