



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

711 Lake Bardwell Dr.
75119-0000, TX Ennis
Phone: 972-875-3413
Fax: 972-875-3174



S11851 6" 15W Led Commercial DNLT 27K/3K/35K/4K/5K 1600L

Satco

Catalog Number	S11851
Manufacturer	Satco
Description	15-Watt Commercial Led Downlight - 6 In. - CCT Adjustable - 120-277 Volts - Econo
Weight per unit	1.1 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.14
average life	50000
Base	Integrated LED
beam angle	90
Lamp Included	Integrated
Lamp Type	LED
Material	Aluminum
Socket Type	Integrated
Voltage Rating	120 to 277 v
Wattage	15

Material, Color, and Finish

Color	White
Finish	white
Style	Utility

Dimensions and Weight

Height	3.46
Length	7.4
Size	H:3.00 D:7.40
Width	7.4



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

711 Lake Bardwell Dr.
75119-0000, TX Ennis
Phone: 972-875-3413
Fax: 972-875-3174

Descriptions

Description	6" 15W LED COMMERCIAL DNLT 27K/3K/35K/4K/5K 1600L
extra long description	SATCO S11851 15WLED/CDL/6/CCT/120-2
Long Description	15-Watt Commercial LED Downlight - 6 in. - CCT Adjustable - 120-277 Volts - Econo
Product Type	15WLED/CDL/6/CCT/120-277
Special Features	Amps: 0.140A;Beam Angle (degree): 90;Bulb Included: Integrated;Can Size: 6 in.;Cct Selectable: True;Ceiling Aperture: 6.02;Color Temp: Warm to Cool White;Fluor Equiv: 1 x 26W CFL;Incandescent Equivalent: 75W;Indoor Outdoor: Indoor;JA8 Compliant: False;Lens Material: Polycarbonate (PC);Location Rating: Wet;Mounting Procedure: Ceiling;NSF Approved: No;Operating Frequency: 50/60Hz;Operating Temp: -20C (-4F) to +40C (+104F);Outdoor;Power Factor: 0.99;Replaceable Light Source: False;Style: Utility;Warranty: 5-Y

Manufacturer Information

Brand	Satco
GTIN	00045923118517
Manufacturers Part Number	S11851
UPC	045923118517

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	RECESSED LIGHTING

Trade Size

aperture size	6.02.
---------------	-------

Packaging

Carton	1
Package	8
Weight Per each	1.05

Uses, Certifications, and Standards

Application	Recessed
Frequency Rating	50/60 Hz
Mounting standard	CEILING cETLus - Listed