



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S49392 36W Led Hid RPLC 50K Med Base 4968LM

Satco

Catalog Number	S49392
Manufacturer	Satco
Description	36 Watt Led Hid Replacement - 80 Cri - 5000K - Medium Base - Economy Hi-Pro
Weight per unit	1.6 (lbs/each)
Product Category	Lighting

### Features

average life	35000
Base	Medium
beam angle	300
Shape	Corn-cob

### Material, Color, and Finish

Finish	white
--------	-------

### Dimensions and Weight

Size	7.16
------	------

### Descriptions

Description	36W LED HID RPLC 50K MED BASE 4968LM
extra long description	SATCO S49392 36W/LED/HP/850/100-277
Long Description	36 Watt LED HID Replacement - 80 CRI - 5000K - Medium Base - Economy Hi-Pro
Product Type	36W/Led/HP/850/100-277V/E26
Special Features	Lawful for sale in California ; Lumens: 4968 ; CCT: 5000K ; Color Temperature: Natural Light ; Dimmable: Non-Dimmable ; Lamp Appearance: Clear ; MOL: 7.16 in. ; MOD: 3.35 in. ; Weight: 1.57 lb. ; Warranty: 3 Year Limited ; Brand: Hi-Pro ; Enclosure Rating: Enclosed Rated Lamp ; FCC Compliant: Yes ; Ballasting Requirements: Ballast Bypass ; HID Equivalent: 150W ; Indoor/Outdoor: Indoor and Outdoor ; IP Rating: IP65 ; Lamp Ballast: Type B ; Mounting: Base Up, Base Down, or Horizontal ; Operating Temperature:

### Manufacturer Information

Brand	Satco
GTIN	00045923493928
Manufacturers Part Number	S49392
UPC	045923493928



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description ..... LED SPECIALTY LAMPS & MODULES

Type ..... Corncob

## Packaging

Carton ..... 1

Weight Per each ..... 1.57

## Uses, Certifications, and Standards

standard ..... cULus Classified - cULus Listed