

Specifications



Eaton S811+N37N3S

Eaton S811+ soft starter, 65mm 37 A with OPT Inside the Delta

General specifications

PRODUCT NAME	Eaton S811+ soft starter
CATALOG NUMBER	S811+N37N3S
UPC	786685558899
PRODUCT LENGTH/DEPTH	11 in
PRODUCT HEIGHT	11.5 in
PRODUCT WIDTH	9 in
PRODUCT WEIGHT	7.8 lb
CERTIFICATIONS	Contact Manufacturer

Photo is representative



Product specifications

AMPERAGE RATING	37A
SPECIAL FEATURES	30 second ramp or 450% current limit at 50°C, inside-the-delta connection
TYPE	Severe duty
FRAME SIZE	N
RATING	10 kW at 230 V, 18.5 kW at 380-400 V, 18.5 kW at 440 V

Resources

APPLICATION NOTES	S8x1 adjustment - Switching from S801+ to S811+
CATALOGS	Solid-State Motor Control, Reduced Voltage Motor Starters, Volume 6, Tab 1 Product Range Catalog Drives Engineering
MULTIMEDIA	Soft Starter Product Family Overview Soft Starter DS7 up to 32 A Soft starter DS7 up to 200 A
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S811+N37N3S
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Eaton S811+N37N3S

Eaton S811+ soft starter, 65mm 37 A with OPT Inside the Delta

General specifications

PRODUCT NAME	Eaton S811+ soft starter
CATALOG NUMBER	S811+N37N3S
UPC	786685558899
PRODUCT LENGTH/DEPTH	11 in
PRODUCT HEIGHT	11.5 in
PRODUCT WIDTH	9 in
PRODUCT WEIGHT	7.8 lb
CERTIFICATIONS	Contact Manufacturer

Photo is representative



Product specifications

AMPERAGE RATING	37A
SPECIAL FEATURES	30 second ramp or 450% current limit at 50°C, inside-the-delta connection
TYPE	Severe duty
FRAME SIZE	N
RATING	10 kW at 230 V, 18.5 kW at 380-400 V, 18.5 kW at 440 V

Resources

APPLICATION NOTES	S8x1 adjustment - Switching from S801+ to S811+
CATALOGS	Solid-State Motor Control, Reduced Voltage Motor Starters, Volume 6, Tab 1 Product Range Catalog Drives Engineering Soft Starter Product Family Overview
MULTIMEDIA	Soft Starter DS7 up to 32 A Soft starter DS7 up to 200 A
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - S811+N37N3S
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

