

Eaton S811+N37N3S

Catalog Number: S811+N37N3S

Eaton S811+ soft starter, 65mm 37 A with OPT Inside the Delta



General specifications

Product Name	Catalog Number
Eaton S811+ soft starter	S811+N37N3S
UPC	Product Length/Depth
786685558899	11 in
Product Height	Product Width
11.5 in	9 in
Product Weight	Certifications
7.8 lb	Contact Manufacturer

Amperage Rating

37A

Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

Type

Severe duty

Frame size

N

Rating

10 kW at 230 V, 18.5 kW at 380-400 V, 18.5 kW at 440 V

Application notes

S8xL adjustment - Switching from S801+ to S811+

Brochures

S811+/S801+ soft starters

Catalogs

Product Range Catalog Drives Engineering

Product Datasheet - S811+N37N3S

Eaton's Volume 2—Commercial Distribution

Drawings

Type S811+ Soft Starter - N-frame

Installation instructions

Instructions for S811+ Soft Starter, S811+N... and S811+R

Multimedia

Soft starter DS7 up to 200 A

Soft Starter DS7 up to 32 A

Soft Starter Product Family Overview

Specifications and datasheets

Eaton Specification Sheet - S811+N37N3S

Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services

Eaton S811+N37N3S

Catalog Number: S811+N37N3S

Eaton S811+ soft starter, 65mm 37 A with OPT Inside the Delta



General specifications

Product Name	Catalog Number
Eaton S811+ soft starter	S811+N37N3S
UPC	Product Length/Depth
786685558899	11 in
Product Height	Product Width
11.5 in	9 in
Product Weight	Certifications
7.8 lb	Contact Manufacturer

Amperage Rating

37A

Special features

30 second ramp or 450% current limit at 50°C, inside-the-delta connection

Type

Severe duty

Frame size

N

Rating

10 kW at 230 V, 18.5 kW at 380-400 V, 18.5 kW at 440 V

Application notes[S8xL adjustment - Switching from S801+ to S811+](#)**Brochures**[S811+/S801+ soft starters](#)**Catalogs**[Product Range Catalog Drives Engineering](#)[Product Datasheet - S811+N37N3S](#)[Eaton's Volume 2—Commercial Distribution](#)**Drawings**[Type S811+ Soft Starter - N-frame](#)**Installation instructions**[Instructions for S811+ Soft Starter, S811+N... and S811+R](#)**Multimedia**[Soft starter DS7 up to 200 A](#)[Soft Starter DS7 up to 32 A](#)[Soft Starter Product Family Overview](#)**Specifications and datasheets**[Eaton Specification Sheet - S811+N37N3S](#)**Warranty guides**[Selling Policy 25-000 - Distribution and Control Products and Services](#)