



# S9421

13PAR30/SN/LED/60'/3000K/120V/D  
 13 watt PAR30 Short Neck LED; 3000K; 60' beam spread;  
 Medium base; 120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

### Compatible Dimmers

- Lutron® C.L Family of dimmers Gen 2.0-2.1-2.2
- Lutron® MAESTRO MACL-153
- Lutron® CASETEA PPD-6WCL-WH



S9421

| Item Number | UPC          | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base   | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9421       | 045923094217 | 120     | 13    | 50W                     | PAR30SN    | Medium | E26       |

  

| Lamp Code                       | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
|---------------------------------|-----------------------|--------|---------------|---------------|----------------|---------------------|-------------|
| 13PAR30/SN/LED/60'/3000K/120V/D | Dimmable              | Silver | 3 5/8"        | 3.75"         | 950            | 25000               | 3000        |

  

| Color      | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant | UL or ETL Listed |
|------------|-----|-----------------|------|--------------|-------------|----------------|------------------|
| Warm White | 80  | 60              | 12/6 | Box          | ENERGY STAR | Yes            | Yes              |

  

| Warranty       |
|----------------|
| 3 Year Limited |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9421

13PAR30/SN/LED/60'/3000K/120V/D  
 13 watt PAR30 Short Neck LED; 3000K; 60' beam spread;  
 Medium base; 120 volts

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- IP65 - Wet location rated
- For Indoor and Outdoor use
- Dimmable

### Compatible Dimmers

- Lutron® C.L Family of dimmers Gen 2.0-2.1-2.2
- Lutron® MAESTRO MACL-153
- Lutron® CASETEA PPD-6WCL-WH



S9421

| Item Number | UPC          | Voltage | Watts | Incandescent Equivalent | Lamp Shape | Base   | ANSI Base |
|-------------|--------------|---------|-------|-------------------------|------------|--------|-----------|
| S9421       | 045923094217 | 120     | 13    | 50W                     | PAR30SN    | Medium | E26       |

  

| Lamp Code                       | Dimmable/Non-Dimmable | Finish | MOL In Inches | MOD In Inches | Initial Lumens | Average Rated Hours | Kelvin Temp |
|---------------------------------|-----------------------|--------|---------------|---------------|----------------|---------------------|-------------|
| 13PAR30/SN/LED/60'/3000K/120V/D | Dimmable              | Silver | 3 5/8"        | 3.75"         | 950            | 25000               | 3000        |

  

| Color      | CRI | Beam Spread Deg | Pack | Package Type | ENERGY STAR | RoHS Compliant | UL or ETL Listed |
|------------|-----|-----------------|------|--------------|-------------|----------------|------------------|
| Warm White | 80  | 60              | 12/6 | Box          | ENERGY STAR | Yes            | Yes              |

  

| Warranty       |
|----------------|
| 3 Year Limited |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

