



# S9622

9.5BR30/LED/4000K/830L/120V/D  
9.5 watt; BR30 LED; 105° beam spread; 4000K; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9622

| Item Number      | Product Line                | UPC                            | Voltage         | Watts         | Incandescent Equivalent | Power Factor   | Lamp Shape          |
|------------------|-----------------------------|--------------------------------|-----------------|---------------|-------------------------|----------------|---------------------|
| S9622            | DiTTO™                      | 045923096228                   | 120             | 9.5           | 65W                     | 0.91           | BR30                |
| Base             | ANSI Base                   | Lamp Code                      | Finish          | MOL In Inches | MOD In Inches           | Initial Lumens | Average Rated Hours |
| Medium           | E26                         | 9.5BR30/LED/4000K/830L/120V/D  | Frosted         | 5 3/16"       | 3.75"                   | 830            | 25000               |
| Kelvin Temp      | Color                       | CRI                            | Beam Spread Deg | Pack          | Package Type            | ENERGY STAR    | RoHS Compliant      |
| 4000             | Cool White                  | 80                             | 105             | 12/6          | Box                     | ENERGY STAR    | Yes                 |
| UL or ETL Listed | UL Classification           | Warranty                       |                 |               |                         |                |                     |
| Yes              | cULus - Damp Location Rated | <a href="#">3 Year Limited</a> |                 |               |                         |                |                     |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027





# S9622

9.5BR30/LED/4000K/830L/120V/D  
9.5 watt; BR30 LED; 105° beam spread; 4000K; Medium base;  
120 volts; Dimmable

### Features

- Solid State LED lighting
- Reflector replacement lamp
- Long life
- Dimmable



S9622

| Item Number      | Product Line | UPC                           | Voltage         | Watts         | Incandescent Equivalent | Power Factor                   | Lamp Shape          |
|------------------|--------------|-------------------------------|-----------------|---------------|-------------------------|--------------------------------|---------------------|
| S9622            | DiTTO™       | 045923096228                  | 120             | 9.5           | 65W                     | 0.91                           | BR30                |
| Base             | ANSI Base    | Lamp Code                     | Finish          | MOL In Inches | MOD In Inches           | Initial Lumens                 | Average Rated Hours |
| Medium           | E26          | 9.5BR30/LED/4000K/830L/120V/D | Frosted         | 5 3/16"       | 3.75"                   | 830                            | 25000               |
| Kelvin Temp      | Color        | CRI                           | Beam Spread Deg | Pack          | Package Type            | ENERGY STAR                    | RoHS Compliant      |
| 4000             | Cool White   | 80                            | 105             | 12/6          | Box                     | ENERGY STAR                    | Yes                 |
| UL or ETL Listed |              | UL Classification             |                 |               |                         | Warranty                       |                     |
| Yes              |              | cULus - Damp Location Rated   |                 |               |                         | <a href="#">3 Year Limited</a> |                     |



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
www.satco.com

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027

