



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SC20 Tinned Copper Splice- Standard Barrel, 2/0 Awg

*Nsi Industries*

|                  |                                                                                                                                                                                                                                                                                                                                                       |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | SC20                                                                                                                                                                                                                                                                                                                                                  |
| Manufacturer     | Nsi Industries                                                                                                                                                                                                                                                                                                                                        |
| Description      | Standardbarrel TINNEDCOPPERSPLICE2/0 Awg Standard Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed. |
| Weight per unit  | 0.0700 (lbs/each)                                                                                                                                                                                                                                                                                                                                     |
| Product Category | Large Terminals & Connectors                                                                                                                                                                                                                                                                                                                          |

### Features

|                      |        |
|----------------------|--------|
| Material             | Copper |
| Number of Conductors | 2      |
| Poles                | 1      |
| Voltage Rating       | 600 V  |
| Warranty             | 1 YEAR |

### Material, Color, and Finish

|        |            |
|--------|------------|
| Color  | Black      |
| Finish | Tin Plated |

### Dimensions and Weight

|      |                            |
|------|----------------------------|
| Size | L=1.75 - OD=.560 - ID=.440 |
|------|----------------------------|

### Descriptions

|                        |                                                                                                                                                                                                                                                                                                                                                       |
|------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | TINNED COPPER SPLICE- STANDARD BARREL, 2/0 AWG                                                                                                                                                                                                                                                                                                        |
| extra long description | NSI SC-2/0 2/0 AWG Copper Short Bar                                                                                                                                                                                                                                                                                                                   |
| Features               | StandardBarrel TinnedCopperSplice2/0 AWG Standard Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Long Description       | StandardBarrel TinnedCopperSplice2/0 AWG Standard Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Product Type           | 2/0 Awg Copper Short Barrel Splice - Black                                                                                                                                                                                                                                                                                                            |
| Special Features       | 2/0 AWG (STR) - CU Splice                                                                                                                                                                                                                                                                                                                             |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381037077 |
| Manufacturers Part Number | SC-2/0         |
| UPC                       | 662381037077   |

## Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Short Barrel - CU Splice          |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 25   |
| Weight Per each | 0.07 |

## Uses, Certifications, and Standards

|                          |                                         |
|--------------------------|-----------------------------------------|
| Application              | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C                                    |
| standard                 | UL486                                   |
| Temperature Rating       | 90 C                                    |