

Project Name

Location

Prepared By



SATCO S8738

20WA21/LED/5K/120-277V

Notes

(www) 01-22-2023 03:00:07

General

Status	Discontinued
Substitute	S28737
Watts	20W
Incandescent Equivalent	150W
Volts	120V-277V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80
Lumens	2910L
Beam Spread	280
Dimmable	Non-Dimmable
Hours Rated	25000
Product Category	Type A
Technology	LED

Electrical

Operating Frequency	50/60Hz
Candlepower	209
Power Factor	>0.9
Operating Temperature	-25C (-13F) to +45C (+113F)

Physical

MOL	5
MOD	2.63
Housing Color	White
Weight (lb.)	0.34

Additional Information

Rated For Enclosed Fixture	Yes
Min Compartment Size	Length: 8.50 in. Width: 6 in. Depth: 6 in.
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus - Certified; cULus - Classified; cULus - Listed
Location Rating	Damp
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

Project Name

Location

Prepared By



SATCO S8738

20WA21/LED/5K/120-277V

Notes

[\[www\] 01-12-2023 03:00:07](#)

General

Status	Discontinued
Substitute	S28737
Watts	20W
Incandescent Equivalent	150W
Volts	120V-277V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	Frost
CCT (Kelvin)	5000K
Temperature	Natural Light
CRI	80
Lumens	2910L
Beam Spread	280
Dimmable	Non-Dimmable
Hours Rated	25000
Product Category	Type A
Technology	LED

Electrical

Operating Frequency	50/60Hz
Candlepower	209
Power Factor	>0.9
Operating Temperature	-25C (-13F) to +45C (+113F)

Physical

MOL	5
MOD	2.63
Housing Color	White
Weight (lb.)	0.34

Additional Information

Rated For Enclosed Fixture	Yes
Min Compartment Size	Length: 8.50 in. Width: 6 in. Depth: 6 in.
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus - Certified; cULus - Classified; cULus - Listed
Location Rating	Damp
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
Colorado Status	Lawful for sale
Hawaii Status	Lawful for sale
Nevada Status	Lawful for sale
Vermont Status	Lawful for sale
Washington Status	Lawful for sale
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp