


Alligator/Battery Booster/Battery



Style	Amp Rating	Material/Plating	Clip Jaws Open	Jaw Length	Wire Attachment	Use w/ Insulator #	Part Number*	Fig. No.
Alligator	5	Steel/Nickel	5/16"	9/16"	Crimp/Screw	Insulated	SC-63 ²	1
Alligator	5	Steel/Nickel	5/16"	5/8"	Crimp/Solder	62	SC-60	2
Alligator	5	Steel/Nickel	5/16"	5/8"	Crimp/Screw	62	SC-60S	3
Alligator	5	Steel/Nickel	5/16"	5/8"	Crimp/Solder	72	SC-70	4
Alligator	5	Steel/Nickel	5/16"	5/8"	Screw/Solder	Ins. Barrel	SC-60HS	5
Alligator	5	Steel/Nickel	5/16"	5/8"	Threaded	62	SC-60TBO	6
Alligator	10	Copper	5/16"	9/16"	Crimp/Screw	Insulated	SC-63C ²	1
Alligator	10	Copper	5/16"	5/8"	Crimp/Screw	62	SC-60CS	3
Alligator	10	Copper	5/16"	5/8"	Screw/Solder	Ins. Barrel	SC-60CHS	5
Battery Booster	200	Steel/Copper	1-9/16"	1-1/16"	Crimp/Solder	Insulated	SC-41A ¹	7
Battery Booster	400	Copper	1-9/16"	1-1/16"	Crimp/Solder	Insulated	SC-41C ¹	7
Battery	25	Steel/Zinc	3/4"	7/16"	Crimp/Screw	26	SC-24A	8

* Contact Sales Department for different types of packaging available.

1 Handles are insulated.

2 Comes with pre-attached protective insulator.



"Leadership is a potent combination of strategy and character. But if you must be without one, be without the strategy"

— Henry Ford

Plug-in content

Our Products

- [Batteries](#)
- [Battery and Test Clips](#)
- [Chemicals](#)
- [Fasteners](#)
- [Flashlights](#)
- [Hand Tools](#)
- [Selecta Packaged Products](#)
- [Switches](#)
- [Terminals](#)

PRODUCT SEARCH

Customer Service

Our customer service staff are ready to assist you. To contact our staff [click here >](#)

Product Catalog

Download our full product catalog to your desktop and take it with you on the road. [Click here >](#)

[Home >>](#) Item Detail

Browse Our Catalog

Item Code **SC-41CR-BU**

Cross Reference

Clip, Hippo, Copper, 400 Amp, 1 9/16 op

Description

Clip, Hippo, Copper, 400 Amp, 1 9/16" opening, Red

[Add to RFQ](#)

UOM

Vendor

MUELLER ELECTRIC COMPANY

Pkg Size


1

Unit Size

1

[Continue Shopping](#)

Alligator/Battery Booster/Battery



Style	Amp Rating	Material/Plating	Clip Jaws Open	Jaw Length	Wire Attachment	Use w/ Insulator #	Part Number*	Fig. No.
Alligator	5	Steel/Nickel	5/16"	9/16"	Crimp/Screw	Insulated	SC-63 ²	1
Alligator	5	Steel/Nickel	5/16"	5/8"	Crimp/Solder	62	SC-60	2
Alligator	5	Steel/Nickel	5/16"	5/8"	Crimp/Screw	62	SC-60S	3
Alligator	5	Steel/Nickel	5/16"	5/8"	Crimp/Solder	72	SC-70	4
Alligator	5	Steel/Nickel	5/16"	5/8"	Screw/Solder	Ins. Barrel	SC-60HS	5
Alligator	5	Steel/Nickel	5/16"	5/8"	Threaded	62	SC-60TBO	6
Alligator	10	Copper	5/16"	9/16"	Crimp/Screw	Insulated	SC-63C ²	1
Alligator	10	Copper	5/16"	5/8"	Crimp/Screw	62	SC-60CS	3
Alligator	10	Copper	5/16"	5/8"	Screw/Solder	Ins. Barrel	SC-60CHS	5
Battery Booster	200	Steel/Copper	1-9/16"	1-1/16"	Crimp/Solder	Insulated	SC-41A ¹	7
Battery Booster	400	Copper	1-9/16"	1-1/16"	Crimp/Solder	Insulated	SC-41C ¹	7
Battery	25	Steel/Zinc	3/4"	7/16"	Crimp/Screw	26	SC-24A	8

* Contact Sales Department for different types of packaging available.

1 Handles are insulated.

2 Comes with pre-attached protective insulator.



"Leadership is a potent combination of strategy and character. But if you must be without one, be without the strategy"

—Henry Ford

Plug-in content

Our Products

- [Batteries](#)
- [Battery and Test Clips](#)
- [Chemicals](#)
- [Fasteners](#)
- [Flashlights](#)
- [Hand Tools](#)
- [Selecta Packaged Products](#)
- [Switches](#)
- [Terminals](#)

PRODUCT SEARCH

Customer Service

Our customer service staff are ready to assist you. To contact our staff [click here >](#)

Product Catalog

Download our full product catalog to your desktop and take it with you on the road. [Click here >](#)

[Home >>](#) Item Detail

Browse Our Catalog

Item Code **SC-41CR-BU**

Cross Reference

Description **Clip, Hippo, Copper, 400 Amp, 1 9/16 op**Description **Clip, Hippo, Copper, 400 Amp, 1 9/16" opening, Red**[Add to RFQ](#)UOM Vendor **MUELLER ELECTRIC COMPANY**Pkg Size **1**Unit Size **1**[Continue Shopping](#)