



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SC9120LBL *Delisted* Smoke/CRB-Mnox 10YR Life BRK Brands/Ademco/First Alert

Catalog Number	SC9120LBL
Manufacturer	BRK Brands/Ademco/First Alert
Description	Hardwired Combo Smoke & CO Alarm With 10-Year Sealed 9V Lithium Battery Backup. Ac 120V Interconnectable With Silence and Latching Features. Includes Ionization Smoke Sensing Tehcnology and Electrochemical Carbon Monoxide Sensor.
Weight per unit	0.6750 (lbs/each)
Product Category	Smoke & Heat Detectors

Features

alarm type	Audio
dimensions	5.6" diameter x 2.0" height
media	Yes
Operating Voltage	120V AC 60Hz w/ 10-year sealed lithium battery backup
Output Current	0.09 Amps
Sensor Type	Ion / Electrochemical
Temperature Range	40 Degree F (4 Degree C) to 100 Degree F (38 Degree C)

Material, Color, and Finish

Color	White
Enclosure Material	Plastic

Descriptions

Description	*DELISTED* SMOKE/CRB-MNOX 10YR LIFE
extra long description	BRK SC9120LBL 120V AC Smoke/CO Alar
Features	Hardwired Combo smoke & CO alarm with 10-Year sealed 9V lithium battery backup.
Long Description	Hardwired Combo smoke & CO alarm with 10-Year sealed 9V lithium battery backup. AC 120V Interconnectable with Silence and Latching features. Includes Ionization smoke sensing tehcnology and electrochemical carbon monoxide sensor.
Product Type	120V Ac Smoke/CO Alarm-10YR Batt Backup

Manufacturer Information

Brand	BRK
GTIN	00029054015372
Manufacturers Part Number	SC9120LBL
UPC	029054015372

Taxonomies, Classifications, and Categories

Category Description	SMOKE DETECTORS
Type	10-Year Combination Smoke & Carbon Monoxide Alarm



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	12
Weight Per each	0.675

Uses, Certifications, and Standards

Application	Single and or multiple station alarm specifically designed to detect smoke and carbon monoxide in residential and institutional applications including sleeping rooms of hospitals, hotels, motels, dormitories and other multi-family dwellings. This product ships in a 6 pack - perfect for large jobs.
environmental conditions	10 percent to 90 percent relative humidity (RH)
Mounting standard	Electrical junction box, wall or ceiling UL217, UL2034