



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3200 N Central Expwy Suite 100  
75071-0000, TX Mckinney  
Phone: 972-542-1196  
Fax: 972-542-2279



## SE150PLR0 1-1/2"X50' BLK Braid Expnd Sleeve

Panduit Corporation

Catalog Number	SE150PLR0
Manufacturer	Panduit Corporation
Description	The SE150P-LR0 Braided Sleeving Provides Continuous Abrasion Resistance For Wires, Cables, and Tubing. The Lightweight, Durable Protection Is Highly Flexible, and The Open Weave Will Not Trap Heat or Humidity. Complaint With U.S. and European Passenger Rail Standards. Temperature Range: -94°F – 257°F (-70°C – 125°C). Polyethylene Terephthalate. Nominal Diameter: 1.50" (38.1 MM), 50' (15.2 M) Long. Color Black. 1 Per Package.
Weight per unit	1.4 (lbs/each)
Product Category	Cable Ties & Wraps

### Features

Material	PET
media	Yes
Nominal Size	1.50

### Material, Color, and Finish

Color	Black
-------	-------

### Dimensions and Weight

Diameter	1.00 - 2.13
Length	50

### Descriptions

Description	1-1/2"X50' BLK BRAID EXPND SLEEVE
extra long description	PAN SE150P-LR0 SE150P-LR0 Braided E
Long Description	The SE150P-LR0 Braided Sleeving provides continuous abrasion resistance for wires, cables, and tubing. The lightweight, durable protection is highly flexible, and the open weave will not trap heat or humidity. Complaint with U.S. and European passenger rail standards. Temperature range: -94°F – 257°F (-70°C – 125°C). Polyethylene Terephthalate. Nominal Diameter: 1.50" (38.1 mm), 50' (15.2 m) long. Color Black. 1 per package.
Product Type	SE150P-LR0 Braided Expandable Sleeving

### Manufacturer Information

Brand	Panduit®
GTIN	00074983202485
Manufacturers Part Number	SE150P-LR0
UPC	074983202485



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3200 N Central Expwy Suite 100  
75071-0000, TX Mckinney  
Phone: 972-542-1196  
Fax: 972-542-2279

## Taxonomies, Classifications, and Categories

Type ..... Braided Expandable Sleeving .....

## Packaging

Carton ..... 1 .....

Weight Per roll ..... 1.35 .....

## Uses, Certifications, and Standards

Application ..... (1) Provides Continuous Abrasion Protection for Wires, Cables,  
Hoses, and Tubing; (2) Highly Flexible Open Weave will not Trap  
Heat or Humidity; (3) Allows for Use with Irregular Shapes .....

standard ..... CSA Certified, UL Recognized E116868, RoHS Compliant .....

Temperature Rating ..... 257 .....