

Specifications

Eaton SF500PH10X10

Eaton rotary disconnect shaft extension for external handle, Shaft for PH2 handle, I-, J-, K-, L-, M-frame, Shaft extension, 100-400A, 500mm (19.7 in), Shaft extensions for external handles, R9, Handle type: PH2, PH3



Photo is representative

General specifications

PRODUCT NAME	Eaton rotary disconnect shaft extension
CATALOG NUMBER	SF500PH10X10
UPC	786685408538
PRODUCT LENGTH/DEPTH	19.7 in
PRODUCT HEIGHT	0.39 in
PRODUCT WIDTH	0.39 in
PRODUCT WEIGHT	0.85 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	Contact Manufacturer



Physical Attributes

SERIES R9

Performance Ratings

AMPERAGE RATING 100-400A

TYPE	Shaft extension
-------------	-----------------

Miscellaneous	
PRODUCT CATEGORY	Shaft extensions for external handles
SIZE	500 mm (19.7 in)
SPECIAL FEATURES	Shaft for PH2 handle, I-,J-,K-,L-,M-frame
USED WITH	Handle type: PH2, PH3

Resources	
MULTIMEDIA	Switching Devices Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SF500PH10X10
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.



Specifications

Eaton SF500PH10X10

Eaton rotary disconnect shaft extension for external handle, Shaft for PH2 handle, I-,J-,K-,L-,M-frame, Shaft extension, 100-400A, 500mm (19.7 in), Shaft extensions for external handles, R9, Handle type: PH2, PH3



Photo is representative

General specifications

PRODUCT NAME	Eaton rotary disconnect shaft extension
CATALOG NUMBER	SF500PH10X10
UPC	786685408538
PRODUCT LENGTH/DEPTH	19.7 in
PRODUCT HEIGHT	0.39 in
PRODUCT WIDTH	0.39 in
PRODUCT WEIGHT	0.85 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	Contact Manufacturer



Powering Business Worldwide

Physical Attributes

SERIES R9

Performance Ratings

AMPERAGE RATING 100-400A

TYPE	Shaft extension
-------------	-----------------

Miscellaneous	
PRODUCT CATEGORY	Shaft extensions for external handles
SIZE	500 mm (19.7 in)
SPECIAL FEATURES	Shaft for PH2 handle, I-,J-,K-,L-,M-frame
USED WITH	Handle type: PH2, PH3

Resources	
MULTIMEDIA	Switching Devices Flex Center
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - SF500PH10X10
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.

All other trademarks are property of their respective owners.

