



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## SHC1043CR Cordcon, STR ML, .88-1.00", 1", Nyl, Gy *Hubbell Wiring Devices*

Catalog Number	SHC1043CR
Manufacturer	Hubbell Wiring Devices
Description	Kellems Wire Management, Cord Connectors, Straight Male, .88"-1.00", 1", Nylon
Weight per unit	0.2000 (lbs/each)
Product Category	Cable & Cord Grips

### Features

Number of Conductors	Single
pallet quantity	4725

### Material, Color, and Finish

Color	Gray
Color Code	GRAY

### Dimensions and Weight

Size	1.88 in x 1.88 in x 2.45 in
------	-----------------------------

### Descriptions

Description	CORDCON, STR ML, .88-1.00", 1", NYL, GY
extra long description	HWDK SHC1043CR CORDCON, STR ML, .88
Features	Cord Connectors - Hubbell has the broadest line and the widest choice of materials in the industry. NPT hub sizes from ¼" to 3" in straight male end, 90°, 45°, female and underground feed connectors. They are available in your choice of aluminum, plated steel, nylon and stainless steel. The zinc-plated steel cord connectors offers the strength of steel and the corrosion resistance of zinc-plating. These heavy-duty connectors hold up to most manufacturing chemicals including acid solutions, solvents and oth
Long Description	Kellems Wire Management, Cord Connectors, Straight Male, .88"-1.00", 1", Nylon
Product Type	Cordcon, STR ML, .88-1.00", 1", Nyl, Gy
Special Features	Standard Product

### Manufacturer Information

Brand	WIRING DEVICE-KELLEMS
GTIN	00783585208152
Manufacturers Part Number	SHC1043CR
series	Standard Duty
UPC	783585208152



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	STRAIGHT MALE

## Packaging

Carton	1
Package	15
Weight Per each	0.2

## Uses, Certifications, and Standards

Application	Straight Male- Form 4
environmental conditions	Suitable for use in wet locations when used with a listed nylon washer between box and fitting.
Mounting	Locknut or Tapped Opening
nema rating	12;4;4X;NEMA Type 4, 4X, 12 and 13
standard	UL Listed