

SL2261 -- Universal 2-Cycle Oil, 15 Fl Oz



Product Description

Power equipment oil is a 40/50 to 1 oil designed to withstand high heat which is encountered in small horsepower engines (25 horsepower or less) work in injector or fuel lubricant engines.

Product Specifications

Applications	For engines of 25 horsepower or less such as: 2-Cycle Motorcycles, Motor Scooters, Mopeds, Mini-Bikes, Lawn Mowers, Chain Saws, Garden Equipment, Power Generators, Auxiliary Pumps, and Refrigeration Equipment
Unit Package Description	15 Ounce Bottle
Generic Description 1	Universal 2-Cycle Oil
Brand	Sta-Lube
Net Fill	15 Fl Oz
UPC Code	0 72213 22610 2
Unit Dimensions-Inches	7.56H x 1.63W x 3.75D
Units Per Case	12
Case Dimensions-Inches	6.5H x 10.25W x 13D
Cases Per Pallet	133
Lbs. Per Case	13
I 2 of 5 Code	30072213226103
Appearance	Blue Oily Liquid
Odor	Faint Petroleum
Flashpoint - TCC Method	>151°F
Specific Gravity	0.883
Flammability	Combustible
Plastic Safe	Yes
DOT Proper Shipping Name	Not Regulated
VOC % (Federal)	14
VOC g/L (Federal)	124
VOC Lbs./Gal. (Federal)	1.09
VOC Compliant For CA	Not Regulated
VOC Compliant For OTC/ LADCO	Not Regulated
VOC Category/Limit	Not Regulated

SL2261 -- Universal 2-Cycle Oil, 15 Fl Oz



Product Description

Power equipment oil is a 40/50 to 1 oil designed to withstand high heat which is encountered in small horsepower engines (25 horsepower or less) work in injector or fuel lubricant engines.

Product Specifications

Applications	For engines of 25 horsepower or less such as: 2-Cycle Motorcycles, Motor Scooters, Mopeds, Mini-Bikes, Lawn Mowers, Chain Saws, Garden Equipment, Power Generators, Auxiliary Pumps, and Refrigeration Equipment
Unit Package Description	15 Ounce Bottle
Generic Description 1	Universal 2-Cycle Oil
Brand	Sta-Lube
Net Fill	15 Fl Oz
UPC Code	0 72213 22610 2
Unit Dimensions-Inches	7.56H x 1.63W x 3.75D
Units Per Case	12
Case Dimensions-Inches	6.5H x 10.25W x 13D
Cases Per Pallet	133
Lbs. Per Case	13
I 2 of 5 Code	30072213226103
Appearance	Blue Oily Liquid
Odor	Faint Petroleum
Flashpoint - TCC Method	>151°F
Specific Gravity	0.883
Flammability	Combustible
Plastic Safe	Yes
DOT Proper Shipping Name	Not Regulated
VOC % (Federal)	14
VOC g/L (Federal)	124
VOC Lbs./Gal. (Federal)	1.09
VOC Compliant For CA	Not Regulated
VOC Compliant For OTC/ LADCO	Not Regulated
VOC Category/Limit	Not Regulated