

BLANK PLATES -- BOX MOUNTED, THREE GANG, LIGHT ALMOND

SP33LA | [Pass & Seymour](#)



FEATURES & BENEFITS

3-GANG BLANK BOX MOUNTED LA



- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent, and moisture.
- Nominal thickness, .070 inch.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Size: Standard
Type: Box Mount
Style: Blank Plate

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121704
UR: No

DIMENSIONS

Weight: 1.61009

TECHNICAL INFORMATION

Material: Thermoset Plastic

Capacity: 3-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA

BLANK PLATES -- BOX MOUNTED, THREE GANG, LIGHT ALMOND

SP33LA | [Pass & Seymour](#)



FEATURES & BENEFITS

3-GANG BLANK BOX MOUNTED LA



- Molded of non-combustible mar-proof material.
- Available in "SP" series in Standard, Junior-Jumbo, and Jumbo sizes.
- Seven standard colors available -- Ivory, White, Brown, Gray, Black, Red, and Light Almond.
- Individually wrapped with color-matching screws.
- Resistant to discoloration, grease, oil, solvent, and moisture.
- Nominal thickness, .070 inch.

SPECIFICATIONS

GENERAL INFO

Color: Light Almond
Size: Standard
Type: Box Mount
Style: Blank Plate

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
CSA Listing Info: Yes
CUL Listing No: No
cULus: No
cURus: No
Federal Spec: No
UL Listing No: Yes
UN SPSC: 39121704
UR: No

DIMENSIONS

Weight: 1.61009

TECHNICAL INFORMATION

Material: Thermoset Plastic

Capacity: 3-gang

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: CHINA