



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



SPJ2 Plastic Wallplate JR Jumbo 2G 2 Toggle W/Out Line

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | SPJ2 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Smooth Wall Platejunior-Jumbo 2-Gang Toggle |
| Weight per unit | 0.1213 (lbs/each) |
| Product Category | Wall Plates & Covers |

Features

| | |
|-----------------|---------------|
| cutout | Toggle |
| indoor/outdoor | Indoor |
| insulation | Bare |
| Mounting Type | Strap Mounted |
| Number of Gangs | 2 |
| orientation | Vertical |
| Wall Plate Type | Toggle Switch |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|-----------|------|
| Size | 5" |
| Thickness | 0.07 |

Descriptions

| | |
|------------------------|---|
| Construction | Plastic |
| Description | PLASTIC WALLPLATE JR JUMBO 2G 2 TOGGLE W/OUT LINE |
| extra long description | P&S SPJ2 PLT PLST JR JUMBO 2G 2TOG |
| Long Description | Smooth Wall PlateJunior-Jumbo 2-Gang Toggle |
| Product Type | PLT PLST JR Jumbo 2G 2TOG W/O Line |
| Special Features | Standard size plastic smooth wall plate |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007680836 |
| Manufacturers Part Number | SPJ2 |
| UPC | 785007680836 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | Wall Plate |

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 120 |
| Weight Per each | 0.1213 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|------------------------|
| Application | Residential/Commercial |
| Mounting | WALL |
| standard | UL, CSA, CSA, UL514 |