

CONNECTORS

Service Post Connectors One-Wire Type

SPM SERIES



FEATURES

- Made from high copper content hard-drawn rod; used for connecting one or two conductors.
- Lay-in feature makes them excellent for continuous loop grounding and bonding.
- Used to ground to bar or plate.
- Suitable for direct burial in earth or concrete.

RATINGS



CAT. NO.	CONDUCTOR RANGE	STUD SIZE	HEX NUT	STD. CTN. QTY.
SPM-1L	12 SOL - 8 STR	0.250 X 20-1	0.375 X 24	25
SPM-2L	8 SOL - 7 STR	0.250 x 20-1	0.437 x 20	25
SPM-3L	10 SOL - 4 STR	0.312 x 18-1	0.500 x 20	25
SPM-4L	6 SOL - 3 STR	0.375 x 16 – 1.125	0.562 x 18	12
SPM-5L	4 STR - 2 STR	0.375 x 16 – 1.125	0.625 x 18	12
SPM-6L	6 SOL - 1/0 STR	0.500 x 13 – 1.250	0.750 x 16	12
SPM-7L	1 SOL - 2/0 STR	0.500 x 13 – 1.250	0.875 x 14	6
SPM-9L	3/0 SOL - 4/0 STR	0.625 x 11 – 1.500	1.125 X 11	3

CONNECTORS
Service Post Connectors
Two-Wire Type
SPM SERIES



FEATURES

- Made from high copper content hard-drawn rod; used for connecting one or two conductors.
- Lay-in feature makes them excellent for continuous loop grounding and bonding.
- Used to ground to bar or plate.
- Suitable for direct burial in earth or concrete.

CAT. NO.	CONDUCTOR RANGE	STUD SIZE	HEX NUT	STD. CTN. QTY.
SPM-21L	12 SOL - 8 STR	0.250 x 20 – 1	0.375 x 24	25
SPM-22L	10 SOL - 7 STR	0.250 x 20 – 1	0.437 x 20	25
SPM-23L	8 SOL - 5 STR	0.312 x 18 – 1	0.500 x 20	25
SPM-24L	6 SOL - 3 STR	0.375 x 16 – 1.125	0.562 x 18	12
SPM-25L	10 SOL - 2 STR	0.375 x 16 – 1.125	0.625 x 18	12
SPM-26L	4 SOL - 1/0 STR	0.500 x 13 – 1.250	0.750 x 16	12
SPM-27L	2 SOL - 2 STR	0.500 x 13 – 1.250	0.875 x 14	6
SPM-29L	1 SOL - 4/0 STR	0.625 x 11 – 1.500	1.125 X 11	3