

# Eaton STE8W

Catalog Number: STE8W

Eaton Sectional wallplate, Wallplate, White, Duplex receptacle, Cutout, Polycarbonate, Single- gang, Mid-size, End piece



## General specifications

Product Name	Catalog Number
Eaton sectional wallplate	STE8W
UPC	Product Length/Depth
032664578540	0.08 in
Product Height	Product Width
4.87 in	3.12 in
Product Weight	Compliances
0.048 lb	RoHS Compliant
Certifications	
cULus Listed	
UL Listed	

## Product specifications

### Special features

End piece

### Type

Wallplate

### Cutout

Duplex receptacle

### Wallplate size

Mid-size

### Color

White

### Number of gangs

1

### Material

Polycarbonate

## Resources

### Catalogs

[Arrow Hart Buyer Guide Section K](#)

### Multimedia

[Wiring devices wallplates](#)

### Specifications and datasheets

[Eaton Specification Sheet - STE8W](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton STE8W

Catalog Number: STE8W

Eaton Sectional wallplate, Wallplate, White, Duplex receptacle, Cutout, Polycarbonate, Single- gang, Mid-size, End piece



## General specifications

Product Name	Catalog Number
Eaton sectional wallplate	STE8W
UPC	Product Length/Depth
032664578540	0.08 in
Product Height	Product Width
4.87 in	3.12 in
Product Weight	Compliances
0.048 lb	RoHS Compliant
Certifications	
cULus Listed	
UL Listed	

## Product specifications

### Special features

End piece

### Type

Wallplate

### Cutout

Duplex receptacle

### Wallplate size

Mid-size

### Color

White

### Number of gangs

1

### Material

Polycarbonate

## Resources

### Catalogs

[Arrow Hart Buyer Guide Section K](#)

### Multimedia

[Wiring devices wallplates](#)

### Specifications and datasheets

[Eaton Specification Sheet - STE8W](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)