

Eaton T27

Catalog Number: T27

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, T shape, 3/4"

General specifications



| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body | T27 |
| | UPC |
| | 782274626505 |
| Product Length/Depth | Product Height |
| 6.25 in | 2.63 in |
| Product Width | Product Weight |
| 2 in | 1.59 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

12

Product specifications

Shape

T

Trade size

3/4"

Material

Feraloy iron alloy

Resources

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

Installation instructions

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - T27](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton T27

Catalog Number: T27

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, T shape, 3/4"

General specifications



| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body | T27 |
| | UPC |
| | 782274626505 |
| Product Length/Depth | Product Height |
| 6.25 in | 2.63 in |
| Product Width | Product Weight |
| 2 in | 1.59 lb |

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

12

Product specifications

Shape

T

Trade size

3/4"

Material

Feraloy iron alloy

Resources

Catalogs

[Crouse-Hinds series Form 7 catalog page](#)

Certification reports

[Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification](#)

[Condulet Form 7 Conduit Outlet Bodies and Covers UL certification](#)

Installation instructions

[IF 964 - Conduit Body Wire Pulling](#)

[IF 863 - Conduit Body Wire Pulling](#)

Specifications and datasheets

[Condulet Form 7 Industrial Grade Conduit Bodies](#)

[Eaton Specification Sheet - T27](#)

Technical service bulletins

[Industrial Fittings Bend Radius and Cubic Capacity Chart](#)

[Industrial Fittings Wire Fill Chart](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)