

Specifications

Eaton T27 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, T shape, 3/4"



Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	T27 SA
UPC	782274626659
PRODUCT LENGTH/DEPTH	6.25 in
PRODUCT HEIGHT	2.63 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.64 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Product specifications

SHAPE	T
TRADE SIZE	3/4"
MATERIAL	Copper-free aluminum

Resources

CATALOGS	Crouse-Hinds series Form 7 catalog page
CERTIFICATION REPORTS	Condulet Form 7 Conduit Outlet Bodies and Covers UL certification Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification
INSTALLATION INSTRUCTIONS	IF 863 - Conduit Body Wire Pulling IF 964 - Conduit Body Wire Pulling
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - T27 SA Condulet Form 7 Industrial Grade Conduit Bodies
TECHNICAL SERVICE BULLETINS	Industrial Fittings Bend Radius and Cubic Capacity Chart Industrial Fittings Wire Fill Chart

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton T27 SA

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Copper-free aluminum, T shape, 3/4"



Photo is representative



General specifications

PRODUCT NAME	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
CATALOG NUMBER	T27 SA
UPC	782274626659
PRODUCT LENGTH/DEPTH	6.25 in
PRODUCT HEIGHT	2.63 in
PRODUCT WIDTH	2 in
PRODUCT WEIGHT	0.64 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

Product specifications

SHAPE	T
TRADE SIZE	3/4"
MATERIAL	Copper-free aluminum

Resources

CATALOGS	Crouse-Hinds series Form 7 catalog page
CERTIFICATION REPORTS	Condulet Form 7 Conduit Outlet Bodies and Covers UL certification Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification
INSTALLATION INSTRUCTIONS	IF 863 - Conduit Body Wire Pulling IF 964 - Conduit Body Wire Pulling
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - T27 SA Condulet Form 7 Industrial Grade Conduit Bodies
TECHNICAL SERVICE BULLETINS	Industrial Fittings Bend Radius and Cubic Capacity Chart Industrial Fittings Wire Fill Chart

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

