

## TORCH HEAD

### CATALOG NUMBER

---

**T111**



### FEATURES

---

Self-igniting propane torch head

Squeezing the control knob produces an instant flame; releasing it extinguishes the flame

No flame adjusting

Burn tip remains cool during normal use

Operates on its side or upside down

Can withstand 60 MPH (96 KPH) winds without flareout

Fits all standard 14.1 and 16.4 ounce (400 and 465 gram) propane cylinders

### WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**  
+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**  
Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**  
Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**  
Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**

## TORCH HEAD

### CATALOG NUMBER

---

**T111**



### FEATURES

---

Self-igniting propane torch head

Squeezing the control knob produces an instant flame; releasing it extinguishes the flame

No flame adjusting

Burn tip remains cool during normal use

Operates on its side or upside down

Can withstand 60 MPH (96 KPH) winds without flareout

Fits all standard 14.1 and 16.4 ounce (400 and 465 gram) propane cylinders

### WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**  
+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

**Europe**  
Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**  
Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**  
Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**