

# Specifications

Photo is representative



## Eaton T20P11S5016

Eaton General purpose ventilated transformer, NEMA 2, FR843A, 60 Hz, 50 kVA, Single-phase, 240X480V, 120/240 V, NEMA ST-20, 1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%, 50 kVA, 240 X 480 Vac-120/240 V, 3XA, DOE 2016

### Physical Attributes

<b>COIL MATERIAL</b>	Aluminum
<b>ENCLOSURE</b>	NEMA 2
<b>FRAME</b>	FR843A
<b>INSULATION</b>	220 °C
<b>MOUNTING</b>	Floor or wall, upright only
<b>TAP SIZE</b>	1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%
<b>TYPE</b>	Energy-efficient ventilated type DS-3 transformer
<b>WIRING CONNECTION</b>	3XA

### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose ventilated transformer
<b>CATALOG NUMBER</b>	T20P11S5016
<b>UPC</b>	786680147647
<b>PRODUCT LENGTH/DEPTH</b>	24.38 in
<b>PRODUCT HEIGHT</b>	38.7 in
<b>PRODUCT WIDTH</b>	23.51 in
<b>PRODUCT WEIGHT</b>	408 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	DOE2016 Efficient
<b>CERTIFICATIONS</b>	UL Listed OSHPD Certified
<b>CATALOG NOTES</b>	10 CFR Part 431 (2016) Efficient

# Specifications

Photo is representative



## Eaton T20P11S5016

Eaton General purpose ventilated transformer, NEMA 2, FR843A, 60 Hz, 50 kVA, Single-phase, 240X480V, 120/240 V, NEMA ST-20, 1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%, 50 kVA, 240 X 480 Vac-120/240 V, 3XA, DOE 2016

### Physical Attributes

<b>COIL MATERIAL</b>	Aluminum
<b>ENCLOSURE</b>	NEMA 2
<b>FRAME</b>	FR843A
<b>INSULATION</b>	220 °C
<b>MOUNTING</b>	Floor or wall, upright only
<b>TAP SIZE</b>	1 at +5%, 2 at -5% x 2 at +2.5%, 4 at -2.5%
<b>TYPE</b>	Energy-efficient ventilated type DS-3 transformer
<b>WIRING CONNECTION</b>	3XA

### General specifications

<b>PRODUCT NAME</b>	Eaton General purpose ventilated transformer
<b>CATALOG NUMBER</b>	T20P11S5016
<b>UPC</b>	786680147647
<b>PRODUCT LENGTH/DEPTH</b>	24.38 in
<b>PRODUCT HEIGHT</b>	38.7 in
<b>PRODUCT WIDTH</b>	23.51 in
<b>PRODUCT WEIGHT</b>	408 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>COMPLIANCES</b>	DOE2016 Efficient
<b>CERTIFICATIONS</b>	UL Listed OSHPD Certified
<b>CATALOG NOTES</b>	10 CFR Part 431 (2016) Efficient