



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832

## T81448GC840DIR 14W Led T8 48" 40K Ballast Compatible

*Rab Lighting*

Catalog Number	T81448GC840DIR
Manufacturer	Rab Lighting
Description	Linear Tubes 2200 Lumens T8 14W Pet Coated Glass 80CRI 4000K Ballast Compatible
Weight per unit	0.4850 (lbs/each)
Product Category	Lighting

### Features

amperage rating	Ballast Dependent:120V Ballast Dependent: 277V
average life	50000
Ballast Type	Type A, Plug and Play
Base	G13
beam angle	180
Fixture Type	Linear Tubes
lumens	2200
Shape	T8
total harmonic distortion	=25%
Voltage Rating	Ballast Dependent
Wattage	14

### Material, Color, and Finish

Color	White
color rendering index (cri)	80
color temperature	4000 (Cool White)
Finish	Matte

### Dimensions and Weight

Length	4
--------	---



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3706 Frankston Hwy  
75701-0000, TX Tyler  
Phone: 903-509-9882  
Fax: 903-509-9832

## Descriptions

Description	14W LED T8 48" 40K BALLAST COMPATIBLE
extra long description	RAB T8-14-48GC-840-DIR T8 LED PET G
Long Description	LINEAR TUBES 2200 LUMENS T8 14W PET COATED GLASS 80CRI 4000K BALLAST COMPATIBLE
Product Type	T8 Led Pet Glass 4FT Type A 14W 4K 2200LM
Special Features	Direct Replacement for Fluorescent Lamps: F32T8/32W, F32T8/30W, F32T8/28W, F32T8/25W Easy to install plug and play that requires no rewiring, no tools, no instructions 50,000 hour Lifespan Rated for use in enclosed and open fixtures in dry or damp locations Diffused frosted lens will maintain the same light quality over time Compatible with most instant start electronic T8 ballasts, Please check Compatibility List Approximately 40% more efficient than fluorescent T8 lamps Instant on full brightness Environmentally

## Manufacturer Information

Brand	Rab Lighting
GTIN	00019813833606
Manufacturers Part Number	T8-14-48GC-840-DIR
UPC	019813833606

## Taxonomies, Classifications, and Categories

Category Description	LED LINEAR STRAIGHT(Fluor replacement), U-SHAPE & CIRCULAR LAMPS
Type	Tubes

## Packaging

Carton	1
Package	25
Weight Per each	0.485

## Uses, Certifications, and Standards

Application	Indoor Lamps
-------------	--------------