

**Thermal  
T&B Catalog Number:**

TA25DU11  
66201988550  
Active

**UPC Number:****Status:****Description:**

3 pole thermal overload relay with 7.5-11.0 amp setting range

**Features**

Economic overload protection

Comes with RESET, TEST, and STOP functions

Automatic and manual reset

**Application**Offers reliable protection for motors in the event of  
overload or phase failure

For use with single and three phase motors

**General**

Series	TA25DU
Poles	3
For Contactors	A/E/L9 through A/E/L40 and A/E/L9N00 through A/ E/L26N1
Output Contacts	1 NC and 1 NO
Trip Class	10A
Reset Type	Manual/Automatic

**Dimension Information**

H x W x D (inches)	3.70 x 1.73 x 3.70
--------------------	--------------------

**Specifications**

Amp Setting Range (A)	7.5-11.0
-----------------------	----------

**Packaging**

T&B Inner Pack	1
Package in Units	48
T&B Sold in UOM	Each
T&B Weight Per UOM	0.39 lbs. Each

**Certifications**

Approvals	UL, CSA, CE
-----------	-------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com

**Thermal  
T&B Catalog Number:**

TA25DU11  
66201988550  
Active

**UPC Number:****Status:****Description:**

3 pole thermal overload relay with 7.5-11.0 amp setting range

**Features**

Economic overload protection

Comes with RESET, TEST, and STOP functions

Automatic and manual reset

**Application**Offers reliable protection for motors in the event of  
overload or phase failure

For use with single and three phase motors

**General**

Series	TA25DU
Poles	3
For Contactors	A/E/L9 through A/E/L40 and A/E/L9N00 through A/ E/L26N1
Output Contacts	1 NC and 1 NO
Trip Class	10A
Reset Type	Manual/Automatic

**Dimension Information**

H x W x D (inches)	3.70 x 1.73 x 3.70
--------------------	--------------------

**Specifications**

Amp Setting Range (A)	7.5-11.0
-----------------------	----------

**Packaging**

T&B Inner Pack	1
Package in Units	48
T&B Sold in UOM	Each
T&B Weight Per UOM	0.39 lbs. Each

**Certifications**

Approvals	UL, CSA, CE
-----------	-------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com