

# Specifications

## Eaton TA27

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, TA shape, 3/4"



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	TA27
<b>UPC</b>	782274630205
<b>PRODUCT LENGTH/DEPTH</b>	6.25 in
<b>PRODUCT HEIGHT</b>	2.63 in
<b>PRODUCT WIDTH</b>	2.88 in
<b>PRODUCT WEIGHT</b>	2.06 lb

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

## Product specifications

SHAPE	TA
TRADE SIZE	3/4"
MATERIAL	Feraloy iron alloy

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Form 7 catalog page</a>
CERTIFICATION REPORTS	<a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers UL certification</a> <a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification</a>
INSTALLATION INSTRUCTIONS	<a href="#">IF 863 - Conduit Body Wire Pulling</a> <a href="#">IF 964 - Conduit Body Wire Pulling</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Condulet Form 7 Industrial Grade Conduit Bodies</a> <a href="#">Eaton Specification Sheet - TA27</a>
TECHNICAL SERVICE BULLETINS	<a href="#">Industrial Fittings Bend Radius and Cubic Capacity Chart</a> <a href="#">Industrial Fittings Wire Fill Chart</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.



# Specifications

## Eaton TA27

Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body, Feraloy iron alloy, TA shape, 3/4"



### General specifications

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series Condulet Form 7 conduit outlet body
<b>CATALOG NUMBER</b>	TA27
<b>UPC</b>	782274630205
<b>PRODUCT LENGTH/DEPTH</b>	6.25 in
<b>PRODUCT HEIGHT</b>	2.63 in
<b>PRODUCT WIDTH</b>	2.88 in
<b>PRODUCT WEIGHT</b>	2.06 lb

## Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	12

## Product specifications

SHAPE	TA
TRADE SIZE	3/4"
MATERIAL	Feraloy iron alloy

## Resources

CATALOGS	<a href="#">Crouse-Hinds series Form 7 catalog page</a>
CERTIFICATION REPORTS	<a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers UL certification</a> <a href="#">Condulet Form 7 Conduit Outlet Bodies and Covers Canadian certification</a>
INSTALLATION INSTRUCTIONS	<a href="#">IF 863 - Conduit Body Wire Pulling</a> <a href="#">IF 964 - Conduit Body Wire Pulling</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Condulet Form 7 Industrial Grade Conduit Bodies</a> <a href="#">Eaton Specification Sheet - TA27</a>
TECHNICAL SERVICE BULLETINS	<a href="#">Industrial Fittings Bend Radius and Cubic Capacity Chart</a> <a href="#">Industrial Fittings Wire Fill Chart</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights  
Reserved.

Eaton is a registered trademark.

All other trademarks are property of  
their respective owners.

Follow us on social media to get the latest  
product and support information.

